




LOC	DIST	REVISIONS				
CM	52	P	LTR	DESCRIPTION	DATE	DWN
			M1	REVISED PER ECO-11-004820	11MAR11	RK
						APVD
						HMR

1. FITS 1.70 – 1.85 DIAMETER HOLE IN A 1.57 PRINTED CIRCUIT BOARD.
2. PARTS TO COMPLY WITH AMP SOLDERABILITY SPECIFICATION 109-11-1.



1.57	.062	2.36	.093	6.22	.245	—	—
0.38	.015	2.34	.092	3.18	.125	10.36	.408
0.32	.013	1.85	.073	2.92	.115	10.29	.405
0.13	.005	1.70	.067	2.44	.096	10.21	.402
MM	IN	MM	IN	MM	IN	MM	IN

CONVERSION TABLE



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. BECK 8-27-97	TE Connectivity			
DIMENSIONS: mm		CHK R. SWING 8-27-97				
		APVD A. BEDDICK 9-10-97	NAME			
		PRODUCT SPEC 108-1025	PIN, .093 DIAMETER, PHOSPHER BRONZE, CLINCH FIT, LOOSE PIECE, P.C. CONTACT			
MATERIAL 0.32 PH BRZ		APPLICATION SPEC 114-1008	SIZE A2	CAGE CODE 00779	DRAWING NO C-61137	RESTRICTED TO —
FINISH PRE TIN		WEIGHT —	CUSTOMER DRAWING		SCALE 15:1	SHEET 1 OF 1
					REV M1	