

# 2.4 GHz External Vehicle or Enclosure Mounted Antenna

Pulse Part Number SLPT2400NMOHF



Pulse is proud to introduce the SLPT (Shadow Low Profile Transit) product line for Public Safety, WLAN, LTE and 3G/4G applications. These rugged, aesthetically pleasing antennas provide a smaller, slimmer option to our current LPT product line without sacrificing mechanical or electrical performance. The product line includes both NMO and tamper-proof direct mount products, which will support multiple cable and connector options.

SLPT antennas were designed to perform over the high-percentage bandwidth applications prevalent in the market today. As a new product line, these antennas were created specifically to serve emerging applications such as 700 MHz Public Safety, LTE, Smart Grid and WLAN. These value-oriented antennas provide a cost-effective, high-performance solution for LTE and 802.11n MIMO applications as well. When combined with our NMOHFGPS antenna, these antennas provide an efficient GPS combination solution.

## Features

- NMO mount models
- Multiple and dual frequency products available
- Shorter, slimmer profile without sacrificing mechanical performance
- IP-67 rating when installed to compliant surface
- RoHS Compliant Product

## Applications

- Public Safety & LTE
- 802.11n Applications
- M2M and Smart Metering

**NOTE:** This antenna requires an NMO high frequency mount. It is recommended the antenna be installed on a Pulse/Larsen NMOHF mount.

# 2.4 GHz External Vehicle or Enclosure Mounted Antenna

Pulse Part Number SLPT2400NMOHF

## Electrical Specifications

Frequency [MHz]	2400 - 2500
Nominal Impedance [ $\Omega$ ]	50
Gain [dBi avg]	4.3
VSWR	2.0:1
Polarization	Vertical
Horizontal Plane	Omni
Power Rating [W]	10

## Environmental Specifications

Operating Temperature [ $^{\circ}\text{C}$ ]	-40 to +85
Storage Temperature [ $^{\circ}\text{C}$ ]	-40 to +85
Relative Humidity [%]	100

## Mechanical Specifications

Radome Material	PC + ABS Plastic
Color	Black
Ingress Protection	IP-67
Weight [oz/g]	2.5 / 70.87
Dimensions [In/mm]	2.5 H x 1.5 $\varnothing$ base / 63.5 x 38.1 $\varnothing$ base
Mounting	NMOHF Mount

**NOTE:** Performance measurements are taken on an 18" (450 mm) diameter ground plane. A similar ground plane size is recommended for optimal performance.

## Radiation Pattern

### Elevation Plane

