




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01_1	REDRAWN IN CAD, UPDATED TO NEW STANDARD PER ECN 92-0010	3B 11/20/92	Com 11/30/92

HOUSING BUSHING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER ASTM-A380
SPRING	STAINLESS STEEL	PASSIVATED
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT CONTACT SLEEVE	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290
CONTACT RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
RETAINING RING	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-C-45204
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		
DRAWN BY BHM DATE 9/14/90		
CHECKED BY JAS 9/26/90		
APPD BY		
AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
TITLE OSP FLOATING FLANGE MOUNT JACK TO OSM JACK ADAPTER		
SIZE B CODE IDENT NO. 26805 4584-4025-02 REV 01_1		
SCALE 2:1		
SHEET 1 OF 1		

ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) 50	Interface Dimensions See OMNI - SPECTRA CATALOG	Temperature Rating -65° to +125°C
Frequency Range (GHz) DC to 18	Mating Characteristics (OSP & OSM):	Vibration MIL-STD-202, Method 204, Condition D
Volt Rating (VRMS MAX) @ Sea Level 500	Insertion (MAX Lbs) 3	Shock MIL-STD-202, Method 213, Condition I
VSWR 1.05 + .005 f(GHz)	Withdrawal (MIN Oz) 1	Thermal Shock MIL-STD-202, Method 107, Condition B
Insertion Loss (dB MAX) .04 √f(GHz)	Force to Engage:	Moisture Resistance MIL-STD-202, Method 106
RF Leakage (dB MIN) (Interface Only, Fully Mated) -(90-f(GHz))	OSP (Lbs MAX) 3	Corrosion - MIL-STD-202, Method 101, Condition B, 5% Salt Spray
Corona, 70,000 Ft (VRMS MIN) 375	OSM (In-Lbs MAX) 2	
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1500	Force to Disengage:	
Contact Resistance (Milliohms MAX)	OSP (Lbs MAX) 1.5	
Center Contact 2.0	OSM (In-Lbs MAX) 2	
Outer Contact 2.0	Center Contact Captivation	
Cable to Housing N/A	Axial (Lbs) 6	
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 1000	Cable Retention	
I.R.(Megohms MIN) 5000	Axial Force (Lbs MIN) N/A	
	Torque (In-Oz MIN) N/A	
	Weight (Grams) TBD	