

Wire-wound Chip Power Inductors (CB series)

CBC3225T101MR



■ Features

- Item Summary
100 μ H(\pm 20%), 270mA, 340mA, 1210
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping 1000pcs

■ Products characteristics table

CaseSize (EIA/JIS)	1210/3225
Inductance	100 μ H(\pm 20%)
Inductance Measuring Frequency	0.1MHz
Rated Current -Saturation Current	270mA
Rated Current -Temperature Rise Current	340mA
DC Resistance (max)	1.82 Ω
Avg. of DC.Resistance	1.4 Ω
Temperature Range	-40°C to 105°C
Self-resonant Frequency (min)	6MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

■ External Dimensions

L	3.2mm \pm 0.2
W	2.5mm \pm 0.2
H	2.5mm \pm 0.2

2014.01.26

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.