


Part Number: SL12 1R008

Ordering Different Lead Types:

Inside Kinked Leads	Use -A after Ametherm's part #
Outside Kinked Leads	Use -B after Ametherm's part #

For example: to order an inside kinked lead use part number SL12 1R008-A



Electrical Specifications:

Resistance @ 25°C	1.0 $\Omega \pm 20\%$
Max Steady State Current Up to 65°C	8.0 A
Max Recommended Energy Rating (Joules)	40.0 J
Actual Failure Point of Instantaneous Energy (Joules)	80.0 J
Resistance @ 100% of Max Current	0.043 Ω
Resistance @ 50% of Max Current	0.094 Ω
Body Temperature @ 100% Current Rating	176 °C
Dissipation Constant	13.22mW/°C
Thermal Time Constant	40 seconds
Max Power up to 65 °C Ambient	3.90 Watts
Material Type	"A"

Mechanical Specifications:

D	12.0 ± 1.0 mm
T	4.0 ± 0.2 mm
Lead Diameter	0.8 ± 0.05 mm
S	7.8 ± 2.0 mm
L	38.0 ± 9.0 mm
Straight Leads Coating Run Down	5.1 ± 0.5 mm
B	5.65 ± 0.75 mm
C	2.15 ± 0.30 mm