






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
—	—					
		C2		REVISED PER ECR-10-013247	25JUN10	HMR



SECTION A-A



SECTION B-B



SECTION C-C

- 1 WIRE RANGE: 1.31mm² (16 AWG).
- 2 INSULATION RANGE 3.10 [.122] MAXIMUM DIAMETER
- 3 FINISH: 0.76μm MINIMUM GOLD OVER 1.27μm MINIMUM NICKEL REQUIRED ON INNER SURFACE, PERMITTED ON OUTER SURFACE.
- 4 FINISH: 2.54μm MINIMUM TIN ON ALL SURFACES IN THIS AREA.
- 5 FINISH: 2.54μm MINIMUM PRE-TIN ALL OVER.

GOLD 3 4	PHOS. BRZ.	1586055-4
PRE-TIN 5	PHOS. BRZ.	1586055-3
GOLD 3 4	BRASS	1586055-2
PRE-TIN 5	BRASS	1586055-1
FINISH:	MATERIAL:	PART NO.

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 15-NOV-2004	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm [INCHES]		CHK D. COLEY 15-NOV-2004				
		APVD D. COLEY 15-NOV-2004	NAME			
		PRODUCT SPEC	TERMINAL, SOCKET VAL-U-LOK(TM)			
MATERIAL		FINISH	APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C=1586055
			WEIGHT	RESTRICTED TO —	SCALE 10:1	SHEET 1 OF 1
			CUSTOMER DRAWING	REV C2		