



Wireless Charging

Rx (Receiving) Coil Units

WR303050-15F5-G

WR444025-17M6-G

WR444030-16F3-G

WR483245-15F5-G


WR483265-15F5-G

Wireless Charging

Overview of Rx Coil Units

FEATURES

- Receiving coils for wireless charging.
- Pre cracked ferrite is available for durable construction.
- Variety of thickness : from 0.50mm to 1.12mm.
- Flexible sheet type is available.
- Custom design is available based on each design requirements.



APPLICATION

Smartphones, cellular phones, handheld mobile terminals, and DSCs

PART NUMBER CONSTRUCTION

W	R	4832	65	-	15	F5	-	G
Wireless charging	Category	LxW Dimensions (mm)		Sheet thickness (mm)		Coil turns	Material	Internal code
	R Rx	3030	30.0x30.0	25	0.25		F5	
		4440	44.0x40.0	30	0.30		F3	
		4832	48.0x32.0	45	0.45		M6	
				50	0.50			
				65	0.65			



○ Halogen-free: Indicates that Cl content is less than 900ppm, Br content is less than 900ppm, and that the total Cl and Br content is less than 1500ppm.

• All specifications are subject to change without notice.

Rx Coil Units

WR303050-15F5-G

■ SHAPE & DIMENSIONS



■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE



LxW Dimensions (mm)	Thickness (mm)max.	Efficiency* (%)ref.	Inductance (μH) [100kHz, 1Vrms]	DC resistance (Ω)max. [25°C]	Part No.
30.0x30.0	1.00	66	12.3	0.41	WR303050-15F5-G

* Contact us for more information.

Rx Coil Units

WR444025-17M6-G

■ SHAPE & DIMENSIONS



■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE



LxW Dimensions (mm)	Thickness (mm)max.	Efficiency* (%)ref.	Inductance (μH) [100kHz, 1Vrms]	DC resistance (Ω)max. [25°C]	Part No.
43.5x39.5	0.52	68	16.7	0.65	WR444025-17M6-G

* Contact us for more information.

Rx Coil Units

WR444030-16F3-G

■ SHAPE & DIMENSIONS



■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE



LxW Dimensions (mm)	Thickness (mm)max.	Efficiency* (%)ref.	Inductance (μH) [100kHz, 1Vrms]	DC resistance (Ω)max. [25°C]	Part No.
43.5x39.5	0.62	70	19.0	0.70	WR444030-16F3-G

* Contact us for more information.

Rx Coil Units

WR483245-15F5-G

■ SHAPE & DIMENSIONS



■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE



LxW Dimensions (mm)	Thickness (mm)max.	Efficiency* (%)ref.	Inductance (μH) [100kHz, 1Vrms]	DC resistance (Ω)max. [25°C]	Part No.
48.0x32.0	1.00	72	13.0	0.20	WR483245-15F5-G

* Contact us for more information.

Rx Coil Units

WR483265-15F5-G

■ SHAPE & DIMENSIONS



■ ELECTRICAL CHARACTERISTICS

□ CHARACTERISTICS SPECIFICATION TABLE

LxW Dimensions (mm)	Thickness (mm)max.	Efficiency* (%)ref.	Inductance (μH) [100kHz, 1Vrms]	DC resistance (Ω)max. [25°C]	Part No.
48.0x32.0	1.25	73	13.3	0.20	WR483265-15F5-G

* Contact us for more information.