

# Freescale Semiconductor

MPX2100 Rev 10, 10/2008

# 100 kPa On-Chip Temperature Compensated and Calibrated Silicon Pressure Sensors

The MPX2100 series devices silicon piezoresistive pressure sensors providing a highly accurate and linear voltage output directly proportional to the applied pressure. The sensor is a single, monolithic silicon diaphragm with the strain gauge and a thin-film resistor network integrated on-chip. The chip is laser trimmed for precise span and offset calibration an temperature compensation.

#### **Features**

- Temperature Compensated Over 0°C to +85°C
- · Available in Absolute, Differential and Gauge Configurations
- · Easy to Use Chip Carrier Package Options
- · Ratiometric to Supply Voltage
- ±0.25% Linearity (MPX2100D Series)

# MPX2100 Series

0 to 100 kPa (0 to 14.5 psi) 40 mV Full Scale Span (Typical)

# **Application Examples**

- Pump/Motor Controllers
- Robotics
- · Level Indicators
- Medical Diagnostics
- · Pressure Switching
- Barometers

ORDERING INFORMATION									
Device Name	Package Case			# of Ports		Pressure Type		Device	
Device Name	Options	No.	None	Single	Dual	Gauge	Gauge Differential Abs	Absolute	Marking
Unibody Package (	MPX2100 Ser	ies)							
MPX2100A	Tray	344	•					•	MPX2100A
MPX2100D	Tray	344	•				•		MPX2100D
MPX2100AP	Tray	344B		•				•	MPX2100AP
MPX2100GP	Tray	344B		•		•			MPX2100GP
MPX2100DP	Tray	344C			•		•		MPX2100DP
MPX2100GVP	Tray	344D		•		•			MPX2100GVP
MPX2100ASX	Tray	344F		•				•	MPX2100A

#### **PACKAGES**



MPX2100A/D




MPX2100AP/GP CASE 344B-01



MPX2100DP CASE 344C-01



MPX2100GVP CASE 344D-01



MPX2100ASX CASE 344F-01





Figure 1 shows a block diagram of the internal circuitry on the stand-alone pressure sensor chip.




Figure 1. Temperature Compensated Pressure Sensor Schematic

# **Voltage Output versus Applied Differential Pressure**

The differential voltage output of the sensor is directly proportional to the differential pressure applied.

The absolute sensor has a built-in reference vacuum. The output voltage will decrease as vacuum, relative to ambient, is drawn on the pressure (P1) side.

The output voltage of the differential or gauge sensor increases with increasing pressure applied to the pressure side (P1) relative to the vacuum side (P2). Similarly, output voltage increases as increasing vacuum is applied to the vacuum side (P2) relative to the pressure side (P1).



# **Operating Characteristics**

#### **Table 1. Operating Characteristics**

 $(V_S = 10 \text{ Vdc}, T_A = 25^{\circ}\text{C} \text{ unless otherwise noted}, P1 > P2)$ 

Characteristics	Symbol	Min	Тур	Max	Unit
Pressure Range <sup>(1)</sup>	P <sub>OP</sub>	0	_	100	kPa
Supply Voltage <sup>(2)</sup>	V <sub>S</sub>	_	10	16	Vdc
Supply Current	Io	_	6.0	_	mAdc
Full Scale Span <sup>(3)</sup>	V <sub>FSS</sub>	38.5	40	41.5	mV
Offset <sup>(4)</sup> MPX2100D  MPX2100A		-1.0 -2.0	_	1.0 2.0	mV
Sensitivity	ΔV/ΔΡ	_	0.4	_	mV/kPa
Linearity <sup>(5)</sup> MPX2100D  MPX2100A		-0.25 -1.0		0.25 1.0	%V <sub>FSS</sub>
Pressure Hysteresis <sup>(5)</sup> (0 to 100 kPa)	_	_	±0.1	_	%V <sub>FSS</sub>
Temperature Hysteresis <sup>(5)</sup> (-40°C to +125°C)	_	_	±0.5	_	%V <sub>FSS</sub>
Temperature Effect on Full Scale Span <sup>(5)</sup>	TCV <sub>FSS</sub>	-1.0	_	1.0	%V <sub>FSS</sub>
Temperature Effect on Offset <sup>(5)</sup>	TCV <sub>off</sub>	-1.0	_	1.0	mV
Input Impedance	Z <sub>in</sub>	1000	_	2500	Ω
Output Impedance	Z <sub>out</sub>	1400	_	3000	Ω
Response Time <sup>(6)</sup> (10% to 90%)	t <sub>R</sub>	_	1.0	_	ms
Warm-Up	_	_	20	_	ms
Offset Stability <sup>(7)</sup>	_	_	±0.5	_	%V <sub>FSS</sub>

- 1. 1.0 kPa (kiloPascal) equals 0.145 psi.
- 2. Device is ratiometric within this specified excitation range. Operating the device above the specified excitation range may induce additional error due to device self-heating.
- 3. Full Scale Span (V<sub>FSS</sub>) is defined as the algebraic difference between the output voltage at full rated pressure and the output voltage at the minimum rated pressure.
- 4. Offset (Voff) is defined as the output voltage at the minimum rated pressure.
- 5. Accuracy (error budget) consists of the following:

Linearity: Output deviation from a straight line relationship with pressure, using end point method, over the specified

pressure range.

Temperature Hysteresis: Output deviation at any temperature within the operating temperature range, after the temperature is cycled to and

from the minimum or maximum operating temperature points, with zero differential pressure applied.

Pressure Hysteresis: Output deviation at any pressure within the specified range, when this pressure is cycled to and from the minimum

or maximum rated pressure, at 25°C.

TcSpan: Output deviation at full rated pressure over the temperature range of 0 to 85°C, relative to 25°C.

TcOffset: Output deviation with minimum rated pressure applied, over the temperature range of 0 to 85°C, relative to 25°C.

- 6. Response Time is defined as the time for the incremental change in the output to go from 10% to 90% of its final value when subjected to a specified step change in pressure.
- 7. Offset stability is the product's output deviation when subjected to 1000 hours of Pulsed Pressure, Temperature Cycling with Bias Test.

MPX2100



# **Maximum Ratings**

Table 2. Maximum Ratings<sup>(1)</sup>

Rating	Symbol	Value	Unit
Maximum Pressure (P1 > P2)	P <sub>max</sub>	400	kPa
Storage Temperature	T <sub>stg</sub>	-40 to +125	°C
Operating Temperature	T <sub>A</sub>	-40 to +125	°C

<sup>1.</sup> Exposure beyond the specified limits may cause permanent damage or degradation to the device.

#### **LINEARITY**

Linearity refers to how well a transducer's output follows the equation:  $V_{out} = V_{off} + \text{sensitivity x P}$  over the operating pressure range. There are two basic methods for calculating nonlinearity: (1) end point straight line fit (see Figure 2) or (2) a least squares best line fit. While a least squares fit gives the "best case" linearity error (lower numerical value), the calculations required are burdensome.

Conversely, an end point fit will give the "worst case" error (often more desirable in error budget calculations) and the calculations are more straightforward for the user. Motorola's specified pressure sensor linearities are based on the end point straight line method measured at the midrange pressure.




Figure 2. Linearity Specification Comparison



# **On-Chip Temperature Compensation and Calibration**

Figure 3 shows the output characteristics of the MPX2100 series at 25°C. The output is directly proportional to the differential pressure and is essentially a straight line.

The effects of temperature on Full-Scale Span and Offset are very small and are shown under Operating Characteristics.





Figure 3. Output versus Pressure Differential






Figure 4. Cross-Sectional Diagram (not to scale)

Figure 4 illustrates the absolute sensing configuration (right) and the differential or gauge configuration in the basic chip carrier (Case 344). A silicone gel isolates the die surface and wire bonds from the environment, while allowing the pressure signal to be transmitted to the silicon diaphragm.

The MPX2100 series pressure sensor operating characteristics and internal reliability and qualification tests are based on use of dry air as the pressure media. Media other than dry air may have adverse effects on sensor performance and long term reliability. Contact the factory for information regarding media compatibility in your application.



# PRESSURE (P1)/VACUUM (P2) SIDE IDENTIFICATION TABLE

Freescale designates the two sides of the pressure sensor as the Pressure (P1) side and the Vacuum (P2) side. The Pressure (P1) side is the side containing the silicone gel which isolates the die. The differential or gauge sensor is designed to operate with positive differential pressure


applied, P1 > P2. The absolute sensor is designed for vacuum applied to P1 side.

The Pressure (P1) side may be identified by using the table below:

Part Number	Case Type	Pressure (P1) Side Identifier
MPX2100A, MPX2100D	344	Stainless Steel Cap
MPX2100DP	344C	Side with Part Marking
MPX2100AP, MPX2100GP	344B	Side with Port Attached
MPX2100ASX	344F	Side with Port Attached
MPX2100GVP	344D	Stainless Steel Cap



#### **PACKAGE DIMENSIONS**




NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- 2. CONTROLLING DIMENSION: INCH.
  3. DIMENSION -A- IS INCLUSIVE OF THE MOLD STOP RING. MOLD STOP RING NOT TO EXCEED. 16.00 (0.630).

	INCHES		MILLIMETERS		
DIM	MIN	MAX	MIN	MAX	
Α	0.595	0.630	15.11	16.00	
В	0.514	0.534	13.06	13.56	
С	0.200	0.220	5.08	5.59	
D	0.016	0.020	0.41	0.51	
F	0.048	0.064	1.22	1.63	
G	0.100	BSC	2.54 BSC		
J	0.014	0.016	0.36	0.40	
L	0.695	0.725	17.65	18.42	
M	30°	NOM	30° 1	MOV	
N	0.475	0.495	12.07	12.57	
R	0.430	0.450	10.92	11.43	
Υ	0.048	0.052	1.22	1.32	
Z	0.106	0.118	2.68	3.00	

STYLE 1: PIN 1. GROUND 2. + OUTPUT 3. + SUPPLY 4. - OUTPUT STYLE 2: PIN 1. Vcc 2. - SUPPLY 3. + SUPPLY 4. GROUND STYLE 3: PIN 1. GND 2. -VOUT 3. VS 4. +VOUT

#### **CASE 344-15 ISSUE AA UNIBODY PACKAGE**



#### NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
- 2. CONTROLLING DIMENSION: INCH.

	INC	HES	MILLIN	ETERS
DIM	MIN	MAX	MIN	MAX
Α	1.145	1.175	29.08	29.85
В	0.685	0.715	17.40	18.16
С	0.305	0.325	7.75	8.26
D	0.016	0.020	0.41	0.51
F	0.048	0.064	1.22	1.63
G	0.100	BSC	2.54	BSC
Н	0.182	0.194	4.62	4.93
J	0.014	0.016	0.36	0.41
K	0.695	0.725	17.65	18.42
L	0.290	0.300	7.37	7.62
N	0.420	0.440	10.67	11.18
Р	0.153	0.159	3.89	4.04
Q	0.153	0.159	3.89	4.04
R	0.230	0.250	5.84	6.35
S	0.220	0.240	5.59	6.10
U	0.910	BSC	23.11	BSC


STYLE 1: PIN 1. GROUND 2. + OUTPUT 3. + SUPPLY 4. - OUTPUT

**CASE 344B-01 ISSUE B UNIBODY PACKAGE** 

**MPX2100** 



#### **PACKAGE DIMENSIONS**




**CASE 344C-01 ISSUE B UNIBODY PACKAGE** 

NOTES:

- DIMENSIONING AND TOLERANCING PER ANSI
- Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH.

	INC	HES	MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	1.145	1.175	29.08	29.85
В	0.685	0.715	17.40	18.16
С	0.405	0.435	10.29	11.05
D	0.016	0.020	0.41	0.51
F	0.048	0.064	1.22	1.63
G	0.100	BSC	2.54	BSC
Н	0.182	0.194	4.62	4.93
J	0.014	0.016	0.36	0.41
K	0.695	0.725	17.65	18.42
L	0.290	0.300	7.37	7.62
N	0.420	0.440	10.67	11.18
Р	0.153	0.159	3.89	4.04
Ø	0.153	0.159	3.89	4.04
R	0.063	0.083	1.60	2.11
S	0.220	0.240	5.59	6.10
U	0.910	BSC	23.11	I BSC
٧	0.248	0.278	6.30	7.06
W	0.310	0.330	7.87	8.38

STYLE 1: PIN 1. GROUND 2. + OUTPUT 3. + SUPPLY 4. - OUTPUT



**CASE 344F-01 ISSUE B UNIBODY PACKAGE** 


- DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
   CONTROLLING DIMENSION: INCH.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
Α	1.080	1.120	27.43	28.45
В	0.740	0.760	18.80	19.30
С	0.630	0.650	16.00	16.51
D	0.016	0.020	0.41	0.51
Е	0.160	0.180	4.06	4.57
F	0.048	0.064	1.22	1.63
G	0.100	BSC	2.54 BSC	
J	0.014	0.016	0.36	0.41
K	0.220	0.240	5.59	6.10
N	0.070	0.080	1.78	2.03
Р	0.150	0.160	3.81	4.06
Q	0.150	0.160	3.81	4.06
R	0.440	0.460	11.18	11.68
S	0.695	0.725	17.65	18.42
U	0.840	0.860	21.34	21.84
٧	0.182	0.194	4.62	4.92

STYLE 1: PIN 1. GROUND 2. V (+) OUT 3. V SUPPLY 4. V (-) OUT



### **PACKAGE DIMENSIONS**



#### NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
   CONTROLLING DIMENSION: INCH.

_					
	INC	HES	MILLIMETER		
DIM	MIN	MAX	MIN	MAX	
Α	1.145	1.175	29.08	29.85	
В	0.685	0.715	17.40	18.16	
С	0.305	0.325	7.75	8.26	
D	0.016	0.020	0.41	0.51	
F	0.048	0.064	1.22	1.63	
G	0.100	) BSC	2.54 BSC		
Н	0.182	0.194	4.62	4.93	
J	0.014	0.016	0.36	0.41	
K	0.695	0.725	17.65	18.42	
L	0.290	0.300	7.37	7.62	
N	0.420	0.440	10.67	11.18	
Р	0.153	0.159	3.89	4.04	
Q	0.153	0.158	3.89	4.04	
R	0.230	0.250	5.84	6.35	
S	0.220	0.240	5.59	6.10	
U	0.910	910 BSC 23 11 BSC		I BSC	

STYLE 1: PIN 1. GROUND 2. + OUTPUT 3. + SUPPLY 4. - OUTPUT

**CASE 344D-01 ISSUE B UNIBODY PACKAGE** 



#### How to Reach Us:

Home Page:

www.freescale.com

Web Support:

http://www.freescale.com/support

#### **USA/Europe or Locations Not Listed:**

Freescale Semiconductor, Inc.
Technical Information Center, EL516
2100 East Elliot Road
Tempe, Arizona 85284
1-800-521-6274 or +1-480-768-2130
www.freescale.com/support

# Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) www.freescale.com/support

#### Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

#### Asia/Pacific:

Freescale Semiconductor China Ltd. Exchange Building 23F No. 118 Jianguo Road Chaoyang District Beijing 100022 China +86 010 5879 8000 support.asia@freescale.com

#### For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or +1-303-675-2140
Fax: +1-303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale<sup>™</sup> and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc. 2008. All rights reserved.

