

3M

Glass Cloth Tape

361

Technical Data

March, 2014

Product Description 3M™ Glass Cloth Tape 361 is coated with a silicone adhesive for many applications requiring high temperature resistance, high adhesion and a very strong, abrasion-resistant backing.

Product Construction	Backing	Adhesive	Color	Standard Roll Length	Standard Widths
	Glass cloth	Silicone	White	60 yds. (55 m)	1/2, 3/4, 1, 1½, 2, 3 in. (13, 19, 25, 38, 50, 75 mm)

Typical Physical Properties **Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.**

ASTM Test Method		
Adhesion to Steel:	38 oz./in. width (42 N/100 mm)	D-3330
Tensile Strength:	146 lbs./in. width (2555 N/100 mm)	D-3759
Elongation at Break:	9%	D-3759
Backing Thickness:	5.0 mils (0.13 mm)	D-3652
Total Tape Thickness:	6.4 mils (0.16 mm)	D-3652
Temperature Use Range:	-65° to 450°F (-54° to 232°C)	

- Features**
- Can be certified to meet F.A.R. 25.853, flame resistant specification.
 - Can withstand intermittent temperatures up to 550°F (288°C) or higher, depending upon the type and duration of the heat source.
 - Continuous exposure to temperatures above 450°F (232°C) will gradually degrade the adhesive causing loss of tape adhesion and darken the glass cloth backing.

- Application Ideas**
- High temperature applications requiring high tensile strength, good holding power and abrasion resistance.
 - Permanent sealing of high temperature ducts or chambers.
 - As a back up strip for submerged arc welding.
 - Applications requiring heat treatment followed by clean removal of the tape with little or no stain.

3M™ Glass Cloth Tape

361

Storage	Store under normal conditions of 60° to 80°F (16° to 27°C) and 40 to 50% R.H. in the original carton.
Shelf Life	To obtain best performance, use this product within 24 months from date of manufacture.
Product Use	All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.
Warranty and Limited Remedy	Unless stated otherwise in 3M's product literature, packaging inserts or product packaging for individual products, 3M warrants that each 3M product meets the applicable specifications at the time 3M ships the product. Individual products may have additional or different warranties as stated on product literature, package inserts or product packages. 3M MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's application. If the 3M product is defective within the warranty period, your exclusive remedy and 3M's and seller's sole obligation will be, at 3M's option, to replace the product or refund the purchase price.
Limitation of Liability	Except where prohibited by law, 3M and seller will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Business Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (fax)
www.3M.com/iatd



Recycled Paper
40% pre-consumer
10% post-consumer

Printed in U.S.A.
©3M 2014 (3/14)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[361-1"x60yd](#) [361-2x60](#) [361-3/4x60BK](#) [361-3/4x60](#)