






NOTES:

1. RECOMMENDED DRILL SIZE AND ANNULAR RING FOR A 0.37 ϕ FINISHED PTH - REFER TO APPLICATION SPECIFICATION AS-76867-001
2. MINIMUM RECOMMENDED SPACING: 14.00MM
3. MINIMUM PCB THICKNESS: 1.57MM
4. CONNECTOR KEEP OUT AREA

SEE SHEET 1 EC NO: UCP2013-1619 DRAWN BY: DRWNBKINGHAM CHKD: 2012/10/25 APPR: TMCLELL 2012/10/29	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 3:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY KLANG	DATE 2009/05/15	TITLE IPASS PLUS HD 1X4 ASSEMBLY INTERNAL			
				4 PLACES	± ---	± ---	CHECKED BY	DATE				
				3 PLACES	± ---	± .005						
				2 PLACES	± 0.13	± .010	APPROVED BY MBANAKIS		DATE 2010/11/17		 MOLEX INCORPORATED	
				1 PLACE	± 0.25	± ---						
				ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-76867-003		2 OF 4	
							THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

J

I

H

G

F


E

D

C

B

A



J

I

H

G

F

E

D

C

B

A

SEE SHEET 1 EC NO: UCP2013-1619 DRAWN BY: BINGHAM 2012/10/25 CHKD: TMCLELL 2012/10/29 APPR: TMCLELL	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 8:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY DATE KLANG 2009/05/15		TITLE IPASS PLUS HD 1X4 ASSEMBLY INTERNAL			
			4 PLACES	± ---	± ---	CHECKED BY DATE					
			3 PLACES	± ---	± .005	APPROVED BY DATE MBANAKIS 2010/11/17		MOLEX INCORPORATED			
			2 PLACES	± 0.13	± .010						
			1 PLACE	± 0.25	± ---						
			ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE CHART		SD-76867-003		3 OF 4				
REV			SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

13 12 11 10 9 8 7 6 5 4 3 2 1

J

I

H

G

F




E

D

C

B

A



NOTES:

- 0.05 MINIMUM KEEP OUT FOR SOLDER MASK AROUND ALL PADS
- DATUM D TARGETS ARE DEFINED BY THE RESPECTIVE PAD CENTER LINES AND THE LEADING EDGE OF THE TARGET PADS

SEE SHEET 1
EC NO: UCP2013-1619
DRAWN BY: BINGHAM 2012/10/25
CHKD:
APPR: TMCLELL 2012/10/29
REV B8

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± ---	± ---
3 PLACES	± ---	± .005
2 PLACES	± 0.13	± .010
1 PLACE	± 0.25	± ---

ANGULAR ± 1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY: KLANG DATE: 2009/05/15

CHECKED BY: DATE:

APPROVED BY: MBANAKIS DATE: 2010/11/17

MATERIAL NO.

SIZE C

SCALE
8:1

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

TITLE
IPASS PLUS HD
1X4 ASSEMBLY
INTERNAL

MOLEX INCORPORATED

DOCUMENT NO.
SD-76867-003

SHEET NO.
4 OF 4

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION