






ISS.	AMEND	DATE
1	1st DRAWN	21/12/07
2	SPECN / PACKING ADD	15/01/07
3	Ø2.1 VARIANT DEL	21/11/12



SPECIFICATION (WITH APPROVED PLUG)
 RATED: 10A / 20V 4.3uF
 INSERTION FORCE: 2.5Kg max
 WITHDRAWAL FORCE: 1.0Kg-2.5Kg
 INSULATION RESISTANCE: >500MΩ@500VDC
 WITHSTAND VOLTAGE: 250VAC/1 MIN
 CONTACT RESISTANCE: <7mΩ



SUPPLIED TAPED + REELED 100x PER REEL

ROHS
✓
COMPLIANT

0 DEC. PLACE ± 0.30
1 DEC. PLACE ± 0.20
2 DEC. PLACE ± 0.10
HOLE $\varnothing \pm 0.10$
ANGLES $\pm 1/2^\circ$
UNLESS
OTHERWISE STATED

Cliff Electronic Components Ltd.

76 Holmethorpe Avenue, Holmethorpe Industrial Estate,
Redhill, Surrey, RH1 2PF, England, UK
Tel: 01737-771375 Fax: 01737-766012 Website: www.cliffuk.co.uk

THE CONTENTS OF THIS DOCUMENT MUST NOT BE COPIED OR DISCLOSED TO A 3rd PARTY WITHOUT WRITTEN PERMISSION OF CLIFF UK. © 2007

DIMENSIONS IN MILLIMETERS UNLESS OTHERWISE STATED. WORK TO DIMENSIONS. REMOVE ALL BURRS. IF IN DOUBT ASK.		3rd ANGLE PROJECTION: 	DO NOT SCALE
MATERIAL:	PPO / BRASS / SS / COPPER	TITLE: DC POWER SOCKET Ø2.5mm	
FINISH:	AS MOULDED / Sn / Ag PLATED	PACKED ON TAPE / REEL	
DRAWN:	C.A.M.J.	APPROVED: R.W.T.	DRWG. No. FC681495
			FORM: ADDRWGH