


Visit Stancor's Website at [www.stancor.com](http://www.stancor.com)

**Power Transformers**



**Specifications.** Input Voltages: 50/60 Hz; Other voltages available as custom designs. Operating Temperature: -40° to +105°C. Class A insulating materials. Designed to meet requirements of UL 506.

**Single Secondary**

Termination: Primary — leads; Secondary — leads.

Stock No.	Mfr.'s Type	Primary		Secondary		Style	Insulation Test RMS (Volts)	Dimensions (Inches)				Weight (Lbs.)	Agency Certification*	EACH						
		Volts	Volts	Amps	Amps			Case		Mounting					1-49	50-99				
								Case	Mounting	Case	Mounting									
928-3027	P-6465	117	6.3 CT	0.600	A	1500	1.38	2.38	1.50	2.00	—	0.40	UL	<b>6.68</b>	<b>6.22</b>					
928-4040	P-6380	117	6.3	1.000	A	1500	1.76	2.38	1.63	2.38	—	0.60	UL	<b>12.34</b>	<b>11.51</b>					
928-3028	P-6466	117	6.3 CT	3.000	A	2500	2.00	3.25	2.13	2.81	—	1.40	—	<b>11.15</b>	<b>10.39</b>					
928-4752	P-8652	117	10.0 CT	1.000	A	1500	2.00	3.25	2.00	2.81	—	0.90	—	<b>11.91</b>	<b>11.10</b>					
928-6380	P-8380	117	10.0 CT	3.000	A	1500	2.25	3.75	2.25	3.13	—	1.60	—	<b>21.79</b>	<b>20.31</b>					
928-2322	P-8385	117	10.0 CT	6.000	NV	1500	3.13	2.50	2.63	2.00	2.06	3.10	—	<b>19.53</b>	<b>18.20</b>					
928-4045	P-8390	117	12.0	0.150	A	1500	1.23	2.13	2.25	2.75	—	0.25	UL	<b>7.20</b>	<b>6.53</b>					
928-4047	P-8391	117	12.0	0.350	A	1500	1.38	2.38	2.38	2.80	—	0.35	—	<b>7.42</b>	<b>6.82</b>					
928-4048	P-8392	117	12.0	0.700	A	1500	1.75	2.94	1.63	2.38	—	0.60	UL	<b>7.54</b>	<b>7.03</b>					
928-4049	P-8393	117	12.0	1.200	A	1500	2.00	3.25	1.63	2.38	—	0.85	—	<b>9.38</b>	<b>8.75</b>					
928-4757	P-8657	117	12.0	2.000	A	1500	2.00	3.25	2.13	2.81	—	1.30	—	<b>11.30</b>	<b>10.54</b>					
928-4226	P-8658	117	12.0	4.000	A	1500	2.63	4.00	2.25	3.56	—	2.30	—	<b>16.93</b>	<b>14.85</b>					
928-4228	P-8659	117	12.0	6.000	NV	1500	3.50	2.88	2.63	2.25	2.13	3.40	—	<b>21.51</b>	<b>20.05</b>					
928-9860	P-8660	117	12.0	8.000	NV	1500	3.81	3.18	2.75	2.50	2.13	4.30	—	<b>22.24</b>	<b>20.73</b>					
928-4034	P-8384	117	12.6 CT	1.000	A	1500	2.00	3.25	2.13	2.81	—	0.90	—	<b>10.81</b>	<b>11.95</b>					
928-3040	P-8130	117	12.6 CT	2.000	A	1500	2.00	3.25	2.13	2.81	—	1.40	UL	<b>10.90</b>	<b>10.77</b>					
928-6350	P-8358	117	12.6 CT	3.000	A	1500	2.38	3.75	2.25	3.13	—	1.60	—	<b>19.16</b>	<b>17.86</b>					
928-4741	P-8641	117	12.6 CT	4.000	A	1500	2.82	4.00	2.38	3.56	—	2.30	—	<b>17.51</b>	<b>16.32</b>					
928-4018	P-8644	117	12.6 CT	10.000	C	1500	4.23	3.44	3.38	2.75	2.69	6.30	—	<b>40.10</b>	<b>37.38</b>					
928-1009	P-8653	115	14.0 CT	0.250	A	1500	1.38	2.38	2.44	2.00	—	0.40	—	<b>7.81</b>	<b>7.28</b>					
928-4816	P-8691	115	18.0 CT	1.000	A	1500	2.00	3.31	2.13	2.81	—	1.50	—	<b>10.37</b>	<b>9.66</b>					
928-4820	P-8693	115	18.0 CT	2.000	A	1500	2.38	3.75	2.23	3.13	—	2.00	—	<b>12.16</b>	<b>11.33</b>					
928-105	115/230	117	20.0 CT	0.250	A	2500	1.44	2.38	2.38	2.00	—	0.40	—	<b>10.39</b>	<b>9.68</b>					
928-4600	P-8604	117	20.0 CT	1.000	A	1500	2.00	3.25	2.13	2.81	—	1.40	UL	<b>11.48</b>	<b>10.70</b>					
928-9910	P-8651	115	24.0	1.000	A	1500	2.00	3.25	2.13	2.81	—	1.40	—	<b>8.27</b>	<b>7.71</b>					
928-4822	P-8694	115	24.0	2.000	A	1500	2.63	4.00	2.00	3.56	—	2.30	—	<b>13.39</b>	<b>12.48</b>					
928-4059	P-8394	117	24.0 CT	0.085	A	1500	1.38	2.13	1.25	1.75	—	0.23	—	<b>8.05</b>	<b>7.50</b>					
928-5975	P-8395	117	24.0 CT	0.200	A	1500	1.38	2.38	1.38	2.00	—	0.35	UL	<b>7.94</b>	<b>7.40</b>					
928-110	P-8721	230	24.0 CT	0.200	A	1500	1.38	2.38	1.38	2.00	—	0.35	—	<b>10.33</b>	<b>9.63</b>					
928-4200	P-8578	115/230	24.0 CT	0.200	A	1500	1.38	2.38	1.50	2.00	—	0.30	—	<b>10.14</b>	<b>9.46</b>					
928-4052	P-8396	117	24.0 CT	0.400	A	1500	1.75	2.88	1.63	2.38	—	0.60	UL	<b>8.94</b>	<b>8.33</b>					
928-4830	P-8722	230	24.0 CT	0.400	A	1500	1.75	2.88	1.63	2.38	—	0.60	—	<b>13.55</b>	<b>12.64</b>					
928-4053	P-8397	117	24.0 CT	0.700	A	1500	2.00	3.25	1.75	2.81	—	0.85	UL	<b>9.40</b>	<b>8.77</b>					
928-4861	P-8681	117	24.0 CT	1.000	A	1500	2.00	3.25	2.06	2.81	—	1.40	UL	<b>10.04</b>	<b>9.36</b>					
928-4862	P-8662	117	24.0 CT	2.000	A	1500	2.62	4.00	2.38	3.56	—	2.30	—	<b>14.65</b>	<b>13.66</b>					
928-4863	P-8663	117	24.0 CT	4.000	NV	1500	3.81	3.13	2.81	2.13	2.13	4.00	UL	<b>41.00</b>	<b>22.20</b>					
928-9970	P-8664	117	24.0 CT	6.000	NV	1500	4.19	3.44	3.00	2.75	2.25	5.70	—	<b>32.38</b>	<b>30.19</b>					
928-4865	P-8665	117	24.0 CT	8.000	NV	1500	4.19	3.44	3.38	2.75	2.75	7.30	—	<b>36.35</b>	<b>33.88</b>					
928-4824	P-8699	115	24.0 CT	10.000	NV	1500	4.31	3.44	3.50	2.75	3.13	8.00	—	<b>76.95</b>	<b>71.73</b>					
928-3031	P-6469	117	25.2	1.000	A	1500	2.00	3.25	2.13	2.81	—	1.40	—	<b>11.09</b>	<b>10.34</b>					
928-3080	P-8189	117	25.2 CT	1.000	A	1500	2.00	3.25	2.25	2.81	—	1.40	—	<b>10.50</b>	<b>9.79&lt;/</b>					