







LOC		DIST		REVISONS			
CM	53	F	LTR	DESCRIPTION		DATE	DWN
		P		REVISED PER ECO-11-005294		03MAY11	RK



1. NYLON, UL94V-2, NATURAL.
2. DIMENSION TO BE CHECKED AT SURFACE A.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. MALE CONTACTS MUST BE INSERTED SO THAT THE TOP OF THE WIRE AND INSULATION CRIMPS ARE FACING THE SIDE OF THE HOUSING WITH THE LOCKING LATCH.

51.6[2.032]	24	2-794542-4
47.4[1.866]	22	2-794542-2
43.2[1.701]	20	2-794542-0
39[1.535]	18	1-794542-8
34.8[1.370]	16	1-794542-6
30.6[1.205]	14	1-794542-4
26.4[1.039]	12	1-794542-2
22.2[0.874]	10	1-794542-0
18[0.709]	8	794542-8
13.8[0.543]	6	794542-6
9.6[0.378]	4	794542-4
5.4[0.213]	2	794542-2
B	NO. OF POSITIONS	PART NUMBER



DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN R. VESTAL 16MAR99	NAME PLUG, FREE HANGING, 2 TO 24 POSITION, AMP-DUACT™ POWER CONNECTOR
		9 PLC ± 1 PLC ±0.2[0.1] 2 PLC ± 3 PLC ± 4 PLC ±		CHK R. SWING 16MAR99	
		FINISH ±0°10'		APVD C. CASH 16MAR99	
MATERIAL				PRODUCT SPEC	
				APPLICATION SPEC	SIZE A
				WEIGHT	
				CUSTOMER DRAWING	
				SCALE 4:1	

TE Connectivity

AMP-DUACT™ POWER CONNECTOR

00779 794542

SHEET 1 OF 1 REV P