



FCIconnect.com

Copyright FCI



TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S81C4PL00	D09S81C6PL00
15	39.14	33.32	26.32	24.54	19.18	D15S81C4PL00	D15S81C6PL00
25	53.03	47.04	40.04	38.25	33.12	D25S81C4PL00	D25S81C6PL00
37	69.32	63.50	56.50	54.71	49.68	D37S81C4PL00	D37S81C6PL00
						Gold flash	0.76 μ gold


LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	18.00	16.21	10.96	D09S81C4PL00LF	D09S81C6PL00LF
15	39.14	33.32	26.32	24.54	19.18	D15S81C4PL00LF	D15S81C6PL00LF
25	53.03	47.04	40.04	38.25	33.12	D25S81C4PL00LF	D25S81C6PL00LF
37	69.32	63.50	56.50	54.71	49.68	D37S81C4PL00LF	D37S81C6PL00LF
						Gold flash	0.76 μ gold



view shown without plastic pin



Detail of plastic pin



PC card drilling dimensions(after plating)
(thickness 1.60 ±0.20)



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE DRAWING C01-8646-0001

mat'l. code				surface		tolerance		projection		product family																
—				ISO 1302 ✓		ISO 406 ISO 1101				D-SUB																
ltr	ecn no	dr	date	tolerances unless otherwise specified								title														
G	ELX-I-18050	MP	2014/06/23	angles	linear	.0±.0.1						FEMALE CONNECTOR DELTA-D EUROPE RIGHT ANGLED PRESS FIT														
						.00±.0.1																				
				0°±2°		.000±.0.1				scale 2:1		dwg no C01-8646-0576 type Product Customer Drawing														
				dr	BOUTIER		1997/10/22				sheet 1 of 1											size				
				engr	MITHUN PAUL		2014/06/23				A3															
				chr	ALIAS BABU		2014/06/23																			
				appd	BIJU K PAUL		2014/06/23																			
sheet index		revision		G																						
		sheet		1																						