




RED INDICATES ORIGINAL

DASH NO	MODEL NO	LTR CODE	A DIM	B DIM	C DIM	D DIM
-1	CBJR70	—	.24	.050	.090	.0625
-2	CBJR70A	A	.34	.058	.090	.070



INCH	MM
.0010	0.03
.0015	0.04
.005	0.13
.030	0.76
.040	1.02
.050	1.27
.058	1.47
.060	1.52
.0625	1.59
.070	1.78
.090	2.29
.100	2.54
.13	3.30
.24	6.10
.258	6.55
.34	8.64
.380	9.65
1.042	26.47
1.216	30.89

- 6 PRE-TINNED, .0015 MAXIMUM THICKNESS WITH SN63 OR EQUIV SOLDER, PER QQ-S-571, TO WITHIN .060 MAXIMUM OF SHOULDER, AFTER PLATING
- 5 LTR CODE "A" SHOWN IN PHANTOM
4. EXAMPLE OF COMPLETE MODEL NO:
- CBJR70 A — LTR CODE (SEE TABLE) 5
- |
- BASIC MODEL NO (SEE TABLE)
3. FINISH: TFS-1A (NICKEL)
2. CONCENTRIC TWINAX/TRIAX RIGHT ANGLE CIRCUIT BOARD MOUNT TRB SERIES RECEPTACLE
1. ALL DIM ARE IN INCHES

QTY		DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED .XX ± .XXX ± .005 .XXXX ± .0010 ANGLE±		TROMPETER ELECTRONICS, INC.		CBJR70 / A		
DWN	J S 4/20/92	MATERIAL	CODE IDENT	DRAWING NO.		REV
CHK	BW 4/24/92	_____	14949	3-0280		
ENGR						
APPR	✓ 4-23-92	SCALE 4/1	DATE 4-23-92	SHEET 1 OF 2		