


SKiiP 24NAB12T4V10



MiniSKiiP® 2

SKiiP 24NAB12T4V10

Features

- Trench 4 IGBT's
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*


- Inverter up to 22 kVA
- Typical motor power 11 kW

Remarks

- V_{CEsat} , V_F = chip level value
- Case temp. limited to $T_C = 125^\circ\text{C}$ max. (for baseplateless modules $T_C = T_S$)
- product rel. results valid for $T_j \leq 150$ (recomm. Top = $-40 \dots +150^\circ\text{C}$)


Absolute Maximum Ratings

Symbol	Conditions		Values	Unit
Inverter - IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 150 °C	T _s = 25 °C	43	A
		T _s = 70 °C	33	A
I _C	T _j = 175 °C	T _s = 25 °C	48	A
		T _s = 70 °C	39	A
I _{Cnom}			35	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		105	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	µs
T _j			-40 ... 175	°C
Chopper - IGBT				
V _{CES}	T _j = 25 °C		1200	V
I _C	T _j = 150 °C	T _s = 25 °C	43	A
		T _s = 70 °C	33	A
I _C	T _j = 175 °C	T _s = 25 °C	48	A
		T _s = 70 °C	39	A
I _{Cnom}			35	A
I _{CRM}	I _{CRM} = 3 x I _{Cnom}		105	A
V _{GES}			-20 ... 20	V
t _{psc}	V _{CC} = 800 V V _{GE} ≤ 15 V V _{CES} ≤ 1200 V	T _j = 150 °C	10	µs
T _j			-40 ... 175	°C
Inverse - Diode				
V _{RRM}	T _j = 25 °C		1200	V
I _F	T _j = 150 °C	T _s = 25 °C	39	A
		T _s = 70 °C	30	A
I _F	T _j = 175 °C	T _s = 25 °C	44	A
		T _s = 70 °C	35	A
I _{Fnom}			35	A
I _{FRM}	I _{FRM} = 3 x I _{Fnom}		105	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 150 °C		170	A
T _j			-40 ... 175	°C
Freewheeling - Diode				
V _{RRM}	T _j = 25 °C		1200	V
I _F	T _j = 150 °C	T _s = 25 °C	39	A
		T _s = 70 °C	30	A
I _F	T _j = 175 °C	T _s = 25 °C	44	A
		T _s = 70 °C	35	A
I _{Fnom}			35	A
I _{FRM}	I _{FRM} = 3 x I _{Fnom}		105	A
I _{FSM}	t _p = 10 ms, sin 180°, T _j = 150 °C		170	A
T _i			-40 ... 175	°C



NAB

SKiiP 24NAB12T4V10



MiniSKiiP® 2

SKiiP 24NAB12T4V10

Features


- Trench 4 IGBT's
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*

- Inverter up to 22 kVA
- Typical motor power 11 kW

Remarks

- V_{CEsat} , V_F = chip level value
- Case temp. limited to $T_C = 125^\circ\text{C}$ max. (for baseplateless modules $T_C = T_S$)
- product rel. results valid for $T_j \leq 150$ (recomm. Top = $-40 \dots +150^\circ\text{C}$)



NAB


Absolute Maximum Ratings

Symbol	Conditions	Values	Unit
Rectifier - Diode			
V_{RRM}	$T_j = 25^\circ\text{C}$	1600	V
I_F	$T_s = 25^\circ\text{C}, T_j = 150^\circ\text{C}$	81	A
I_{Fnom}		25	A
I_{FSM}	10 ms	$T_j = 25^\circ\text{C}$	A
	sin 180°	$T_j = 150^\circ\text{C}$	A
I^2t	10 ms	$T_j = 25^\circ\text{C}$	A^2s
	sin 180°	$T_j = 150^\circ\text{C}$	A^2s
T_j		-40 ... 150	$^\circ\text{C}$
Module			
$I_{t(RMS)}$	$T_{terminal} = 80^\circ\text{C}, 20\text{A per spring}$	40	A
T_{stg}		-40 ... 125	$^\circ\text{C}$
V_{isol}	AC sinus 50Hz, 1 min	2500	V

Characteristics

Symbol	Conditions	min.	typ.	max.	Unit
Inverter - IGBT					
$V_{CE(sat)}$	$I_C = 35\text{ A}$				
	$V_{GE} = 15\text{ V}$ chipelevel				
V_{CE0}					
r_{CE}	$V_{GE} = 15\text{ V}$				
$V_{GE(th)}$	$V_{GE} = V_{CE}\text{ V}, I_C = 1\text{ mA}$	5	5.8	6.5	V
I_{CES}	$V_{GE} = 0\text{ V}$				
	$V_{CE} = 1200\text{ V}$				
C_{ies}					
C_{oes}					
C_{res}					
Q_G	- 8 V...+ 15 V		200		nC
R_{Gint}	$T_j = 25^\circ\text{C}$		0.00		Ω
$t_{d(on)}$	$V_{CC} = 600\text{ V}$		30		ns
t_r	$I_C = 35\text{ A}$		35		ns
E_{on}	$R_{G on} = 18\ \Omega$		4.3		mJ
$t_{d(off)}$	$R_{G off} = 18\ \Omega$		300		ns
t_f			55		ns
E_{off}	$V_{GE} = +15/-15\text{ V}$		3.25		mJ
$R_{th(j-s)}$	per IGBT		1		K/W
Chopper - IGBT					
$V_{CE(sat)}$	$I_C = 35\text{ A}$				
	$V_{GE} = 15\text{ V}$ chipelevel				
V_{CE0}					
r_{CE}	$V_{GE} = 15\text{ V}$				
$V_{GE(th)}$	$V_{GE} = V_{CE}\text{ V}, I_C = 1\text{ mA}$	5	5.8	6.5	V
I_{CES}	$V_{GE} = 0\text{ V}$				
	$V_{CE} = 1200\text{ V}$				
Q_G	- 8 V...+ 15 V		200		nC
R_{Gint}	$T_j = 25^\circ\text{C}$		0.00		Ω

SKiiP 24NAB12T4V10



MiniSKiiP® 2

SKiiP 24NAB12T4V10

Features


- Trench 4 IGBT's
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised file no. E63532

Typical Applications*

- Inverter up to 22 kVA
- Typical motor power 11 kW

Remarks

- V_{CEsat} , V_F = chip level value
- Case temp. limited to $T_C = 125^\circ\text{C}$ max. (for baseplateless modules $T_C = T_S$)
- product rel. results valid for $T_j \leq 150$ (recomm. Top = $-40 \dots +150^\circ\text{C}$)



NAB

Characteristics					
Symbol	Conditions	min.	typ.	max.	Unit
Chopper - IGBT					
$t_{d(on)}$	$V_{CC} = 600\text{ V}$ $T_j = 150^\circ\text{C}$		30		ns
t_r	$I_C = 35\text{ A}$ $T_j = 150^\circ\text{C}$		35		ns
E_{on}	$R_{G\ on} = 18\ \Omega$ $T_j = 150^\circ\text{C}$		4.3		mJ
$t_{d(off)}$	$R_{G\ off} = 18\ \Omega$ $T_j = 150^\circ\text{C}$		300		ns
t_f	$T_j = 150^\circ\text{C}$		55		ns
E_{off}	$V_{GE} = +15/-15\text{ V}$ $T_j = 150^\circ\text{C}$		3.25		mJ
$R_{th(j-s)}$	per IGBT		1		K/W
Inverse - Diode					
$V_F = V_{EC}$	$I_F = 35\text{ A}$ $V_{GE} = 0\text{ V}$ chiplevel	$T_j = 25^\circ\text{C}$	2.3	2.6	V
		$T_j = 150^\circ\text{C}$	2.3	2.6	V
V_{F0}		$T_j = 25^\circ\text{C}$	1.3	1.5	V
		$T_j = 150^\circ\text{C}$	0.9	1.1	V
r_F		$T_j = 25^\circ\text{C}$	29	32	m Ω
		$T_j = 150^\circ\text{C}$	40	43	m Ω
I_{RRM}	$I_F = 35\text{ A}$ $T_j = 150^\circ\text{C}$		34		A
Q_{rr}	$di/dt_{off} = 1250\text{ A}/\mu\text{s}$ $T_j = 150^\circ\text{C}$		5.6		μC
E_{rr}	$V_{GE} = -15\text{ V}$ $V_{CC} = 600\text{ V}$ $T_j = 150^\circ\text{C}$		2.4		mJ
$R_{th(j-s)}$	per Diode		1.2		K/W
Freewheeling - Diode					
$V_F = V_{EC}$	$I_F = 35\text{ A}$ $V_{GE} = 0\text{ V}$ chiplevel	$T_j = 25^\circ\text{C}$	2.3	2.6	V
		$T_j = 150^\circ\text{C}$	2.3	2.6	V
V_{F0}		$T_j = 25^\circ\text{C}$	1.3	1.5	V
		$T_j = 150^\circ\text{C}$	0.9	1.1	V
r_F		$T_j = 25^\circ\text{C}$	29	32	m Ω
		$T_j = 150^\circ\text{C}$	40	43	m Ω
I_{RRM}	$I_F = 35\text{ A}$ $T_j = 150^\circ\text{C}$		34		A
Q_{rr}	$di/dt_{off} = 1250\text{ A}/\mu\text{s}$ $T_j = 150^\circ\text{C}$		5.6		μC
E_{rr}	$V_{GE} = -15\text{ V}$ $V_{CC} = 600\text{ V}$ $T_j = 150^\circ\text{C}$		2.4		mJ
$R_{th(j-s)}$	per Diode		1.2		K/W
Rectifier - Diode					
$V_F = V_{EC}$	$I_F = 25\text{ A}$ $V_{GE} = 0\text{ V}$ chiplevel	$T_j = 25^\circ\text{C}$	1	1.21	V
		$T_j = 125^\circ\text{C}$		1.1	V
V_{F0}		$T_j = 25^\circ\text{C}$		1.0	V
		$T_j = 125^\circ\text{C}$		0.8	V
r_F		$T_j = 25^\circ\text{C}$	4.8	9.3	m Ω
		$T_j = 125^\circ\text{C}$		11	m Ω
$R_{th(j-s)}$	per Diode		0.9		K/W
Module					
M_s	to heat sink	2		2.5	Nm
w			65		g
Temperatur Sensor					
R_{100}	$T_r = 100^\circ\text{C}$, tolerance = 3 %		1670 $\pm$ 3%		Ω
$R(T)$	$R(T) = 1000\ \Omega [1 + A(T - 25^\circ\text{C}) + B(T - 25^\circ\text{C})^2]$], $A = 7.635 \cdot 10^{-3}\ ^\circ\text{C}^{-1}$, $B = 1.731 \cdot 10^{-5}\ ^\circ\text{C}^{-2}$				




Fig. 1: Typ. output characteristic




Fig. 2: Typ. rated current vs. temperature $I_C = f(T_S)$




Fig. 3: Typ. turn-on /-off energy = $f(I_C)$




Fig. 4: Typ. turn-on /-off energy = $f(R_G)$




Fig. 5: Typ. transfer characteristic












Fig. 6: Typ. gate charge characteristic



pinout, dimensions



These documents are Semikron property. Semikron reserves all copyrights. All copying and transmitting of this information requires written permission. For the case of industrial property rights, Semikron reserves all rights.



- ⊙ power connector
- control connector

pinout

This is an electrostatic discharge sensitive device (ESDS), international standard IEC 60747-1, Chapter IX

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our staff.