



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDM-702-010 REV: 1.0

0.7" 5*7 Dot Matrix Displays

MODEL NO : ELM-702YWA/S117 ECN : Page: 1/5

■ Features :

- Large emitting dot 0.07"diameter.
- Low power/high brightness.

■ Applications:

- Instrument panels
- Digital readout display

■ Description :

- The ELM-702 series are a large emitting area(2.0mm diameter) LED sources configured in a 35 dots 5*7 matrix array.
- These device is made with white dots and gray surface.

PART NO	CHIP		C.C. or C.A.
	Material	Emitted Color	
ELM-702YWA/S117	GaAsP/GaP	Yellow	C.A.

OFFICE : NO. 25,Lane 76,Sec.3, Chung Yang Rd., Tucheng 236, Taipei, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2267-9936

FAX : 886-2-2267-6244,22676189,22676306

<http://www.everlight.com>

TS99052 B991832




0.7" 5*7 Dot Matrix Displays


MODEL NO : ELM-702YWA/S117

ECN : Page: 2/5

■ Package Dimension:



CATHODE ROW
ANODE COLUMN
1 CATHODE ROW 1
2 CATHODE ROW 2
3 ANODE COLUMN 2
4 ANODE COLUMN 1
5 CATHODE ROW 6
6 CATHODE ROW 7
7 ANODE COLUMN 3
8 CATHODE ROW 5
9 ANODE COLUMN 4
10 CATHODE ROW 4
11 CATHODE ROW 3
12 ANODE COLUMN 5



■ NOTES:

- 1.All dimensions are millimeters , tolerance is 0.25mm unless otherwise noted.
 - 2.Above specification may be changed without notice.
- Supplier will reserve authority on material change for above specification.



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number : DDM-702-010 REV: 1.0

0.7" 5*7 Dot Matrix Displays

MODEL NO : ELM-702YWA/S117 ECN : Page: 3/5

■ Absolute maximum ratings at Ta = 25°C :

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	20	mA
Operating Temperature	Topr	-40 to +85	°C
Storage Temperature	Tstg	-40 to +100	°C
Soldering Temperature	Tsol	260 ± 5	°C
Power Dissipation	Pd	85	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	160	mA

■ Electronic optical characteristics :

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous Intensity	Iv	0.45	0.8	----	mcd	If=10mA
Peak Wavelength	λ_p	----	585	----	nm	If=20mA
Dominant Wavelength	λ_d	----	590	----	nm	If=20mA
Spectrum Radiation Bandwidth	$\Delta \lambda$	----	35	----	nm	If=20mA
Forward Voltage	Vf	1.7	2.0	2.6	V	If=20mA
Reverse Current	Ir	----	----	10	μA	Vr=5V



EVERLIGHT ELECTRONICS CO.,LTD.

Device Number :

DDM-702-010

REV:

1.0

0.7" 5*7 Dot Matrix Displays

MODEL NO : ELM-702YWA/S117

ECN :

Page:

4/5

■ Reliability test item and condition:

NO	Item	Test Conditions	Test Hours/Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 SEC	76 PCS	0/1
2	Temperature Cycle	H : +85°C 30min ∫ 5 min L : -55°C 30min	50 CYCLE	76 PCS	0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	50 CYCLE	76 PCS	0/1
4	High Temperature Storage	TEMP : 100°C	1000 HRS	76 PCS	0/1
5	Low Temperature Storage	TEMP : -55°C	1000 HRS	76 PCS	0/1
6	DC Operating Life	If = 20 mA	1000 HRS	76 PCS	0/1
7	High Temperature / High Humidity	85°C/85% RH	1000 HRS	76 PCS	0/1



Device Number : DDM-702-010 REV: 1.0

0.7" 5*7 Dot Matrix Displays

MODEL NO: ELM-702YWA/S117 ECN : Page: 5/5

■ Typical Electro-Optical Characteristic Curves:

