


SPECIFICATION CONTROL DRAWING



Product Revision	Ident Code	Product Dimensions			Cable Dimensions			
		L \pm 1.75 (L \pm 0.075)	φA min	φB min	φD max	φE max	φF min	φG min
SO175-1-00	A	16.50 (0.650)	1.90 (0.075)	2.67 (0.105)	1.90 (0.075)	2.67 (0.105)	0.90 (0.035)	0.50 (0.020)
SO175-2-00	A	16.50 (0.650)	2.67 (0.105)	3.68 (0.145)	2.67 (0.105)	3.68 (0.145)	1.40 (0.055)	0.75 (0.030)
SO175-3-00	A	16.50 (0.650)	4.32 (0.170)	5.08 (0.200)	4.32 (0.170)	5.08 (0.200)	2.15 (0.085)	1.25 (0.050)
SO175-4-00	A	19.10 (0.750)	5.97 (0.235)	6.48 (0.255)	5.97 (0.235)	6.48 (0.255)	3.30 (0.130)	1.80 (0.070)
SO175-5-00	A	19.10 (0.750)	6.98 (0.275)	7.62 (0.300)	6.98 (0.275)	7.62 (0.300)	4.30 (0.170)	2.50 (0.100)


MATERIALS

1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.
2. SOLDER PREFORM WITH FLUX AND THERMAL INDICATOR:
 - SOLDER: TYPE Sn96 per ANSI/J-STD-006.
 - FLUX: TYPE ROM1 per ANSI/J-STD-004.
 - THERMAL INDICATOR: Fusible ring, melt point: 232°C, completely melted at 240°C.
 - MELTABLE RINGS: Environment resistant thermoplastic. Color: blue.

APPLICATION

1. These parts are designed to provide an environment resistant shield termination on cables, rated for 150°C minimum, meeting the dimensional criteria listed, having nickel-plated shields and insulations compatible with the insert material. For compatible insulations, see MIL-S-83519/1 or consult Tyco Electronics/Raychem.
2. When installed per Tyco Electronics/Raychem process standard RCPS-100-70, assemblies will meet performance requirement of Tyco Electronics/Raychem Specification RT-1404, MIL-S-83519, and 514.1920/99 Aerospatiale Matra Specification.
3. Temperature range: -55°C to +175°C.

For best results, prepare the cable as shown:



"G" is the minimum diameter on which the sleeve will seal.

SolderSleeve is a trademark of Tyco Electronics Corporation

tyco Electronics	Tyco Electronics Corporation 300 Constitution Drive, Menlo Park, CA. 94025, U.S.A.		Raychem	TITLE: SOLDERSLEEVE SHIELD TERMINATOR, IMMERSION RESISTANT, 175°C, LEAD-FREE		
Unless otherwise specified dimensions are in millimeters. [Inches dimensions are shown in brackets]				DOCUMENT NO.: SO175-X-00		
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A	ROUGHNESS IN MICRON	Tyco Electronics reserves the right to amend this drawing at any time. Users should evaluate the suitability of the product for their application.	PROD. REV.: SEE TABLE	DOC. ISSUE: 1	DATE: 25-Apr-03
DRAWN BY: M. FORONDA	CAGE CODE: 06090	REPLACES: D020140	DCR NUMBER: D030220	SCALE: None	SIZE: A	SHEET: 1 of 1

If this document is printed it becomes uncontrolled. Check for the latest revision.

© 2004 Tyco Electronics Corporation. All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SO175-3-00](#)