

4HS154

PAGE 1 OF 1

M

DRAWING
NUMBER

4

ISSUE

RELEASE NO. PR-19579 REPLACES

CHECK

CHECK

1 OCT 91


D A W

CHECK

26 SEP 91

T S M

REVISIONS	
A	CO-75825
S	A 15 JULY 93
B	CO-75870
T S M	20 JUL 93
C	CO-94122
T S M	17 MAR 99




NOTES

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø.139 MAX ON 1.000 ± .002 CENTERS
- 2 - FOR USE IN AMBIENT TEMPERATURE RANGE FROM -65°F TO 250°F ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS AT POINT "A"	ELECTRICAL DATA			SCALE	FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — 4-20 OZ	CONTACT ARRANGEMENT			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
RELEASE FORCE — — — 2 OZ MIN	S P D T					
DIFFERENTIAL TRAVEL — — — .100 MAX	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	ONE PLACE (.0)	± .030	
DO NOT OVERTRAVEL MORE THAN --- .062	28 VDC	8 AMP	25 AMP	TWO PLACE (.00)	± .015	
	(SEA LEVEL-1000,000 FT)			THREE PLACE (.000)	± .005	
	125 VAC	1 AMP	.5 AMP	ANGLES	±	
	(SEA LEVEL-70,000 FT)			WEIGHT	6.5 OZ MAX	

FORMTEK

DRAWN