



MODULAR JACKS AND PLUGS: GWLGX Series

Right Angle Ganged Jack with LED

Product Features

Easy Viewing LEDs to Act as Power/Transmit Indicators
 Snap-In Retention Tabs
 Available Fully Shielded for EMI/RFI Protection
 CSA/NRTL Certified File No. LR78160

Performance Specifications

Materials and Finish

Housing Material

Thermoplastic, UL 94V-0 Rated, Black Color

Shield Material

Copper Alloy, Nickel Plated

Contact Material

Phosphor Bronze

Electrical Characteristics

Insulation Resistance

500 Megohms Min.

Contact Resistance

20 milliohms Max.

Current Rating

1.5A

Voltage Rating

125V DC

Operating Temperature

-40°C to +85°C

Durability Rating

500 Mating Cycles Min.

2D Drawing	IGES	STEP	3D PDF
Solder Profile	CofC RoHS Compliant	CofC REACH Compliant	UL Plastic File
Certificate of Origin	Check Stock	Request a Sample	Send Us An Email

Generated Part Number

Part Number Builder

	-				
Series		Shield Option	No. of Ports	No. of Positions & Contacts	LED Color Option

Series

GWLGX - Ganged Modular Jack with LED, Tab Up

Shield Option

S1 - Fully Shielded with Top and Side Grounding Tabs

Number of Ports

2 - 2 Port

4 - 4 Port

8 - 8 Port

Number of Positions/Contacts

88 - 8 Positions / 8 Contacts

LED Color

G/G - Left: Green, Right: Green

Y/G - Left: Yellow, Right: Green

G/Y - Left: Green, Right: Yellow

G/R - Left: Green, Right: Red


R/G - Left: Red, Right: Green

Contact Kycon for Other Options

GWLGX Series

Dimensions in mm

GWLGX-S1288x-x



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kycon:

[GWLGX-S1488-G/Y](#) [GWLGX-S1488-Y/G](#) [GWLGX-S1288-G/Y](#) [GWLGX-S1288-Y/G](#) [GWLGX-S1888-G/Y](#) [GWLGX-S1488-G/G](#) [GWLGX-S1488-R/G](#) [GWLGX-S1288-GR/GR-50](#) [GWLGX-S1888-YG/YG](#) [GWLGX-S1488-R/Y](#) [GWLGX-S1888-GR/GR](#) [GWLGX-S1488-G/R](#) [GWLGX-S1288-GY/GY](#) [GWLGX-S1488-YG/YG](#) [GWLGX-S1888-G/Y-50](#) [GWLGX-S1288-YG/YG](#) [GWLGX-S1288-Y/Y](#) [GWLGX-S1288-Y/G-50](#) [GWLGX-S1488-GY/GY](#) [GWLGX-S1488-Y/Y](#) [GWLGX-S1288-G/R](#) [GWLGX-S1488-G/Y-50](#) [GWLGX-S1888-R/G](#) [GWLGX-S1888-G/G](#) [GWLGX-S1488-GR/GR](#) [GWLGX-S1288-R/G](#) [GWLGX-S1288-G/G](#) [GWLGX-S1288-GY/GY-50](#) [GWLGX-S1888-GY/GY](#) [GWLGX-S1688-G/Y](#) [GWLGX-S1888-R/Y](#) [GWLGX-S1288-GR/GR](#) [GWLGX-S1888-G/R](#) [GWLGX-S1888-Y/G](#) [GWLGX-S1888-Y/Y](#) [GWLGX-S1688Y/G](#) [GWLGX-S1688-Y/G](#)