

EMC housing - HC-B 16-TFQ-76/O1STM25G-EMV - 1642564

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

HEAVYCON sleeve housing B16, for double locking latch, height 76 mm, with thread M25, straight cable outlet, EMC version



Key commercial data

| | |
|--------------------------------------|------------|
| Packing unit | 1 PCE |
| Weight per Piece (excluding packing) | 203.71 GRM |
| Custom tariff number | 85389099 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|--------|-------|
| Height | 76 mm |
| Width | 43 mm |
| Length | 94 mm |

Ambient conditions

| | |
|--------------------------------------|-------------------|
| Degree of protection of housing (IP) | IP65 |
| Ambient temperature (operation) | -40 °C ... 100 °C |

General

| | |
|------------------------------|--|
| Note | For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K |
| Design | B16 |
| Housing type | Sleeve housings |
| Locking type | For double locking latch |
| No. of cable exits | 1 |
| Cable exit | Straight |
| Screw connection | None |
| Type of the screw connection | 1x M25 |

EMC housing - HC-B 16-TFQ-76/O1STM25G-EMV - 1642564

Technical data

General

| | |
|--------------------------|---------------------|
| Housing material | Aluminum die-cast |
| Housing surface material | EMC coating, silver |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440209 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 5.0 | EC000437 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 31261502 |
| UNSPSC 7.0901 | 31261502 |
| UNSPSC 11 | 31261502 |
| UNSPSC 12.01 | 31261502 |
| UNSPSC 13.2 | 31261502 |

Accessories

Accessories

Full screw connection

Cable gland - HC-EMV-KV-M25(9-16,5) - 1690516




EMC screw connection up to 5 bar, thread length: 7.5 mm, cable diameter: 9.0 - 16.5 mm, WAF 29, screw connection: M25


EMC housing - HC-B 16-TFQ-76/O1STM25G-EMV - 1642564

Drawings

Diagram



Dimensioned drawing



Shield attenuation

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>