







Rating		21A 14VDC		Mounting Hole  <table><tr><td>Thickness(mm)</td><td>X(mm)</td><td>Y(mm)</td></tr><tr><td>0.75~1.25</td><td rowspan="3">21.0^{+0.3}₀</td><td>36.6±0.1</td></tr><tr><td>1.25~2.0</td><td>36.8±0.1</td></tr><tr><td>2.0~3.0</td><td>37.0±0.1</td></tr></table>	Thickness(mm)	X(mm)	Y(mm)	0.75~1.25	21.0 ^{+0.3} ₀	36.6±0.1	1.25~2.0	36.8±0.1	2.0~3.0	37.0±0.1	Circuit Diagram 
Thickness(mm)	X(mm)	Y(mm)													
0.75~1.25	21.0 ^{+0.3} ₀	36.6±0.1													
1.25~2.0		36.8±0.1													
2.0~3.0		37.0±0.1													
Contact Resistance		50m ohm Max.													
Insulation Resistance		DC 500V 100M ohm Min.													
Dielectric Strength		AC 1500V 1 minute													
Operation Temperature		- 25 ° ~ + 85 °													
Switch Function		4P SPDT ON-OFF-ON Lamp Dependent													
Lamp Type	LED 12VDC 14V w/resistor														

Material:

1. Frame: Nylon-66(94V-2) - **Black**
Actuator: Nylon-66+33%GF - **Black**
Lens: PC - **White / Black**
Terminal: Silver plated copper
(excepted lamp terminal)
- Printed: None
2. Waterproof: "IP-67".



TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

RoHS Compliant

2	Added Dependent to Function & Lamp Type. 12/19/2011.
1	Changed IP-66 to IP-67. 12/13/10

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/20/10



Rev. 2

Unit: mm

Checked By: *G. Gold*






Title: **ROCKER SWITCH**

CW P/N: **GRB292D201BBWN1**

Rating		21A 14VDC		Mounting Hole 	Circuit Diagram 									
Contact Resistance		50m ohm Max.												
Insulation Resistance		DC 500V 100M ohm Min.												
Dielectric Strength		AC 1500V 1 minute												
Operation Temperature		- 25 ° ~ + 85 °												
Switch Function		4P SPDT ON-OFF-ON Lamp Dependent		<table><tr><td>Thickness(mm)</td><td>X(mm)</td><td>Y(mm)</td></tr><tr><td>0.75~1.25</td><td rowspan="3">21.0^{+0.3}₀</td><td>36.6+0.1</td></tr><tr><td>1.25~2.0</td><td>36.8+0.1</td></tr><tr><td>2.0~3.0</td><td>37.0+0.1</td></tr></table>	Thickness(mm)	X(mm)	Y(mm)	0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1	1.25~2.0	36.8+0.1	2.0~3.0	37.0+0.1
Thickness(mm)	X(mm)	Y(mm)												
0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1												
1.25~2.0		36.8+0.1												
2.0~3.0		37.0+0.1												
Lamp Type	LED 12VDC 14V w/resistor													

Material:

1. Frame: Nylon-66(94V-2) - **Black**
Actuator: Nylon-66+33%GF - **Black**
Lens: PC - **White / Black**
Terminal: Silver plated copper
(excepted lamp terminal)
2. Waterproof: "IP-67".



TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

RoHS Compliant

2	Added Dependent to Function & Lamp Type. 12/19/2011.
1	Changed IP-66 to IP-67. 12/13/10

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/20/10



Rev. 2

Unit: mm

Checked By: *G. Gold*






Title: **ROCKER SWITCH**

CW P/N: **GRB292D201BBWN1**

Rating		21A 14VDC		Mounting Hole 	Circuit Diagram 									
Contact Resistance		50m ohm Max.												
Insulation Resistance		DC 500V 100M ohm Min.												
Dielectric Strength		AC 1500V 1 minute												
Operation Temperature		- 25 ° ~ + 85 °												
Switch Function		4P SPDT ON-OFF-ON Lamp Dependent		<table><tr><td>Thickness(mm)</td><td>X(mm)</td><td>Y(mm)</td></tr><tr><td>0.75~1.25</td><td rowspan="3">21.0^{+0.3}₀</td><td>36.6+0.1</td></tr><tr><td>1.25~2.0</td><td>36.8+0.1</td></tr><tr><td>2.0~3.0</td><td>37.0+0.1</td></tr></table>	Thickness(mm)	X(mm)	Y(mm)	0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1	1.25~2.0	36.8+0.1	2.0~3.0	37.0+0.1
Thickness(mm)	X(mm)	Y(mm)												
0.75~1.25	21.0 ^{+0.3} ₀	36.6+0.1												
1.25~2.0		36.8+0.1												
2.0~3.0		37.0+0.1												
Lamp Type	LED 12VDC 14V w/resistor													

Material:

1. Frame: Nylon-66(94V-2) - **Black**
Actuator: Nylon-66+33%GF - **Black**
Lens: PC - **White / Black**
Terminal: Silver plated copper
(excepted lamp terminal)
2. Waterproof: "IP-67".



TOLERANCE: ±0.3mm UNLESS OTHERWISE SPECIFIED.

RoHS Compliant

2	Added Dependent to Function & Lamp Type. 12/19/2011.
1	Changed IP-66 to IP-67. 12/13/10

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 5/20/10

Rev. 2

Unit: mm

Checked By: *G. Gold*

Title: **ROCKER SWITCH**

CW P/N: **GRB292D201BBWN1**