




TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PBT
FLAMABILITY RATING: UL94-V0
COLOR: WHITE
CONTACT MATERIAL: COPPER ALLOY
CONTACT TYPE: STAMPED
CONTACT PLATING: SELECTIVE GOLD
SHIELDING: STEEL NICKEL PLATED
QUALITY CLASS: 3 AS PER IEC60 603-13

ENVIRONMENTAL
OPERATING TEMPERATURE: -40 UP TO 105°C
COMPLIANCE: LEAD FREE AND ROHS


ELECTRICAL
CURRENT RATING: 3A
WORKING VOLTAGE: 125V AC
INSULATOR RESISTANCE: >5000 MOHM
DIELECTRIC WITHSTANDING VOLTAGE: 1000V AC/MN
CONTACT RESISTANCE: 30 mOHM MAX

STANDARD
 CERTIFIED: E323964 / MODEL NUMBER 618-24F

PACKAGING
TRAY

DIMENSION

PINS	A	B	C	D	E
9	16.33	24.99	30.81	7.90	12.50
15	24.66	33.32	39.14	7.90	12.50
25	38.38	47.04	53.04	7.90	12.50
37	54.84	63.50	69.32	7.90	12.50

RoHS Compliant								
G	26-OCT-10	SHIELDING	GG	PROJECTION: 	GENERAL TOLERANCE	 WÜRTH ELEKTRONIK		
F	07-DEC-09	WORKING VOLT.	JP		.X = +/_ 0.2			
E	19-NOV-09	STANDARD	JP		.XX = +/_ 0.15			
D	01-OCT-09	NEW DRAW	JP					
C	10-FEB-09	DRAW	JP	APPROVAL: RJ	UNIT: MM	DESCRIPTION: FEMALE SOLDER BUCKET		SIZE A4
B	21-FEB-07	DRAW	EC		SCALE:			
A	01-MAR-04	PDF	JP		SHEET: 1/1	WERI PART NO: 618 0xx 249 23		
REV	DATE	FILE	BY		DRAW: MIKE			