19-1177; Rev. 1; 10/02

MAXIM

SOT23, Low-Cost, Low-Dropout, 3-Terminal Voltage References

General Description

The MAX6125/MAX6141/MAX6145/MAX6150/MAX6160 low-dropout, micropower, three-terminal voltage references offer 2.5V, 4.096V, 4.5V, 5.0V, and adjustable (1.23V to 12.4V) output voltages, respectively. Low, 200mV dropout makes these devices ideal for 3V and 5V systems. Unlike two-terminal references that waste battery current and require an external resistor, the MAX61xx family's supply current is virtually independent of input voltage variations, which translates to longer battery life.

Initial accuracy for these devices is ±1%. The output temperature coefficient is typically 15ppm/°C, and guaranteed to be less than 50ppm/°C (except for the MAX6160). The MAX6125/MAX6141/MAX6145/MAX6150 are available in 3-pin SOT23 and 8-pin SO packages. The MAX6160 is available in 4-pin SOT143 and 8-pin SO packages.

Features

- **3-Pin SOT23 Package (MAX6125/MAX6141/MAX6145/MAX6150) 4-Pin SOT143 Package (MAX6160)**
- **Low, 200mV Dropout Voltage**
- **75µA Supply Current, Independent of Input Voltage**
- **15ppm/°C Typical Tempco (50ppm/°C, max)**
- **Stable for All Capacitive Loads up to 10nF**
- **Adjustable Output Voltage from 1.23V to (V_{IN} - 0.2V) (MAX6160)**
- **Optimized for 3V/5V Operation**

Applications

3V/5V Systems

Battery-Powered Systems

Portable and Hand-Held Equipment

Data-Acquisition Systems

Instrumentation and Process Control

Selector Guide

PART	PRESET OUTPUT VOLTAGE (V)	PIN-PACKAGE
MAX6125	2.5	3 SOT23/8 SO
MAX6141	4.096	3 SOT23/8 SO
MAX6145	4.5	3 SOT23/8 SO
MAX6150	5	3 SOT23/8 SO
MAX6160	Adjustable (1.23 to 12.40)	4 SOT143/8 SO

Typical Operating Circuit appears on last page.

Ordering Information

PART	TEMP RANGE	PIN-PACKAGE	TOP MARK
MAX6125ESA	-40°C to +85°C	8 SO	—
MAX6125EUR-T	-40°C to +85°C	3 SOT23-3	EBAA
MAX6141ESA	-40°C to +85°C	8 SO	—
MAX6141EUR-T	-40°C to +85°C	3 SOT23-3	ECAA

Ordering Information continued on last page.

Pin Configurations

TOP VIEW



SO



SOT23-3



SOT143-4

( ) ARE FOR MAX6160 ONLY

For pricing, delivery, and ordering information, please contact Maxim/Dallas Direct! at 1-888-629-4642, or visit Maxim's website at www.maxim-ic.com.

SOT23, Low-Cost, Low-Dropout, 3-Terminal Voltage References

ABSOLUTE MAXIMUM RATINGS

(Voltages With Respect to GND)
IN .....-0.3V to +13.5V
OUT, ADJ.....-0.3V to (V_{IN} + 0.3V)
Output Short-Circuit Duration (to IN or GND).....Continuous
Continuous Power Dissipation (T_A = +70°C)
8-Pin SO (derate 5.9mW/°C above +70°C).....471mW
3-Pin SOT23 (derate 4mW/°C above +70°C).....320mW
4-Pin SOT143 (derate 4mW/°C above +70°C).....320mW
Operating Temperature Range .....-40°C to +85°C
Storage Temperature Range .....-65°C to +160°C
Lead Temperature (soldering, 10s) .....+300°C

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

ELECTRICAL CHARACTERISTICS—MAX6125

(V_{IN} = 2.7V, I_{OUT} = 0mA, T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Supply Voltage	V_{IN}	T_A = T_{MIN} to T_{MAX}	2.7		12.6	V
Output Voltage	V_{OUT}	T_A = +25°C	2.475	2.500	2.525	V
		T_A = T_{MIN} to T_{MAX}	2.450		2.550	
Output Voltage Temperature Coefficient	TCV_{OUT}	T_A = T_{MIN} to T_{MAX}		15	50	ppm/°C
Output Voltage Noise	e_n	0.1Hz to 10Hz		15		μV_{P-P}
		10Hz to 10kHz		500		
Line Regulation	$\Delta V_{OUT}/\Delta V_{IN}$	V_{IN} = 2.7V to 12.6V, T_A = T_{MIN} to T_{MAX}		1	50	µV/V
Load Regulation	$\Delta V_{OUT}/\Delta I_{OUT}$	I_{SOURCE} = 0mA to 1mA		0.4	1	mV/mA
		I_{SINK} = 0mA to 1mA		1.15	10	
Quiescent Supply Current	I_Q	T_A = +25°C		75	100	µA
		T_A = T_{MIN} to T_{MAX}			130	
Change in Supply Current vs. Change in Input Voltage	$\Delta I_Q/\Delta V_{IN}$	V_{IN} = 2.7V to 12.6V		1.7	6	µA/V

ELECTRICAL CHARACTERISTICS—MAX6141

(V_{IN} = 4.3V, I_{OUT} = 0mA, T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Supply Voltage	V_{IN}	T_A = T_{MIN} to T_{MAX}	4.3		12.6	V
Output Voltage	V_{OUT}	T_A = +25°C	4.055	4.096	4.140	V
		T_A = T_{MIN} to T_{MAX}	4.015		4.180	
Output Voltage Temperature Coefficient	TCV_{OUT}	T_A = T_{MIN} to T_{MAX}		15	50	ppm/°C
Output Voltage Noise	e_n	0.1Hz to 10Hz		25		μV_{P-P}
		10Hz to 10kHz		700		
Line Regulation	$\Delta V_{OUT}/\Delta V_{IN}$	V_{IN} = 4.3V to 12.6V, T_A = T_{MIN} to T_{MAX}		2	50	µV/V
Load Regulation	$\Delta V_{OUT}/\Delta I_{OUT}$	I_{SOURCE} = 0mA to 1mA		0.55	1.6	mV/mA
		I_{SINK} = 0mA to 1mA		1.65	16	
Quiescent Supply Current	I_Q	T_A = +25°C		78	105	µA
		T_A = T_{MIN} to T_{MAX}			130	
Change in Supply Current vs. Change in Input Voltage	$\Delta I_Q/\Delta V_{IN}$	V_{IN} = 4.3V to 12.6V		1.7	6	µA/V

ELECTRICAL CHARACTERISTICS—MAX6145

(V_{IN} = 4.7V, I_{OUT} = 0mA, T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Supply Voltage	V_{IN}	T_A = T_{MIN} to T_{MAX}	4.7		12.6	V
Output Voltage	V_{OUT}	T_A = +25°C	4.455	4.500	4.545	V
		T_A = T_{MIN} to T_{MAX}	4.410		4.590	
Output Voltage Temperature Coefficient	TCV_{OUT}	T_A = T_{MIN} to T_{MAX}		15	50	ppm/°C
Output Voltage Noise	e_n	0.1Hz to 10Hz		30		μV_{P-P}
		10Hz to 10kHz		800		
Line Regulation	$\Delta V_{OUT}/\Delta V_{IN}$	V_{IN} = 4.7V to 12.6V, T_A = T_{MIN} to T_{MAX}		2	50	µV/V
Load Regulation	$\Delta V_{OUT}/\Delta I_{OUT}$	I_{SOURCE} = 0mA to 1mA		0.6	1.8	mV/mA
		I_{SINK} = 0mA to 1mA		1.75	18	
Quiescent Supply Current	I_Q	T_A = +25°C		79	105	µA
		T_A = T_{MIN} to T_{MAX}			130	
Change in Supply Current vs. Change in Input Voltage	$\Delta I_Q/\Delta V_{IN}$	V_{IN} = 4.7V to 12.6V		1.7	6	µA/V

ELECTRICAL CHARACTERISTICS—MAX6150

(V_{IN} = 5.2V, I_{OUT} = 0mA, T_A = +25°C, unless otherwise noted.) (Note 1)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Supply Voltage	V_{IN}	T_A = T_{MIN} to T_{MAX}	5.2		12.6	V
Output Voltage	V_{OUT}	T_A = +25°C	4.950	5.000	5.050	V
		T_A = T_{MIN} to T_{MAX}	4.900		5.100	
Output Voltage Temperature Coefficient	TCV_{OUT}	T_A = T_{MIN} to T_{MAX}		15	50	ppm/°C
Output Voltage Noise	e_n	0.1Hz to 10Hz		35		μV_{P-P}
		10Hz to 10kHz		900		
Line Regulation	$\Delta V_{OUT}/\Delta V_{IN}$	V_{IN} = 5.2V to 12.6V, T_A = T_{MIN} to T_{MAX}		1	50	µV/V
Load Regulation	$\Delta V_{OUT}/\Delta I_{OUT}$	I_{SOURCE} = 0mA to 1mA		0.65	2	mV/mA
		I_{SINK} = 0mA to 1mA		1.9	20	
Quiescent Supply Current	I_Q	T_A = +25°C		80	110	µA
		T_A = T_{MIN} to T_{MAX}			145	
Change in Supply Current vs. Change in Input Voltage	$\Delta I_Q/\Delta V_{IN}$	V_{IN} = 5.2V to 12.6V		1.7	6	µA/V

SOT23, Low-Cost, Low-Dropout, 3-Terminal Voltage References

ELECTRICAL CHARACTERISTICS—MAX6160

(V_{IN} = 2.7V; I_{OUT} = 0mA; R1 = 215kΩ ±0.1%, R2 = 208kΩ ±0.1% (circuit of Figure 1); T_A = +25°C; unless otherwise noted.) (Notes 1, 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
Supply Voltage	V_{IN}	T_A = T_{MIN} to T_{MAX}	2.7		12.6	V
Output Voltage Range		T_A = T_{MIN} to T_{MAX}	1.23		V_{IN} - 0.2	V
Output Voltage	V_{OUT}	T_A = +25°C	2.475	2.500	2.525	V
		T_A = T_{MIN} to T_{MAX}	2.450		2.550	
ADJ Feedback Voltage Threshold	V_{ADJ}			1.23		V
ADJ Input Current	I_{ADJ}	V_{ADJ} = 1.23V		70		nA
Output Voltage Temperature Coefficient	TCV_{OUT}	T_A = T_{MIN} to T_{MAX}		15	100	ppm/°C
Output Voltage Noise	e_n	0.1Hz to 10Hz		15		μV_{P-P}
		10Hz to 10kHz		500		
Line Regulation	$\Delta V_{OUT}/\Delta V_{IN}$	V_{IN} = 2.7V to 12.6V, T_A = T_{MIN} to T_{MAX}		1	50	µV/V
Load Regulation	$\Delta V_{OUT}/\Delta I_{OUT}$	I_{SOURCE} = 0mA to 1mA		0.35	1	mV/mA
		I_{SINK} = 0mA to 1mA		1.15	10	
Quiescent Supply Current	I_Q	T_A = +25°C		75	100	µA
		T_A = T_{MIN} to T_{MAX}			130	
Change in Supply Current vs. Change in Input Voltage	$\Delta I_Q/\Delta V_{IN}$	V_{IN} = 2.7V to 12.6V		1.7	6	µA/V

Note 1: All devices are 100% production tested at T_A = +25°C, and are guaranteed by design for T_A = T_{MIN} to T_{MAX} as specified.
Note 2: R1 and R2 program the output voltage in the 1.23V to (V_{IN} - 0.2V) range (see the *Setting the MAX6160 Output Voltage* section).

Typical Operating Characteristics

(V_{IN} = $V_{IN(MIN)}$, I_{OUT} = 0mA, T_A = +25°C, unless otherwise noted.)

SUPPLY CURRENT vs. INPUT VOLTAGE



SUPPLY CURRENT vs. TEMPERATURE



LOAD REGULATION (SOURCING) vs. TEMPERATURE



Typical Operating Characteristics (continued)

(V_{IN} = $V_{IN(MIN)}$, I_{OUT} = 0mA, T_A = +25°C, unless otherwise noted.)

LOAD REGULATION (SINKING) vs. TEMPERATURE



MAX6125/MAX6160 OUTPUT VOLTAGE vs. SOURCE CURRENT



MAX6141 OUTPUT VOLTAGE vs. SOURCE CURRENT



MAX6145 OUTPUT VOLTAGE vs. SOURCE CURRENT



MAX6150 OUTPUT VOLTAGE vs. SOURCE CURRENT



DROPOUT VOLTAGE vs. SOURCE CURRENT



MAX6125/MAX6160 DROPOUT VOLTAGE vs. TEMPERATURE



MAX6141/MAX6145/MAX6150 DROPOUT VOLTAGE vs. TEMPERATURE



MAX6160 ADJ INPUT CURRENT vs. TEMPERATURE



SOT23, Low-Cost, Low-Dropout, 3-Terminal Voltage References

Typical Operating Characteristics (continued)

(V_{IN} = $V_{IN(MIN)}$, I_{OUT} = 0mA, T_A = +25°C, unless otherwise noted.)

CHANGE IN OUTPUT VOLTAGE vs. INPUT VOLTAGE



CHANGE IN OUTPUT VOLTAGE vs. TEMPERATURE



POWER-SUPPLY REJECTION RATIO vs. FREQUENCY



**With respect to output voltage at V_{IN} = $V_{IN(MIN)}$.*

***With respect to output voltage at T_A = +25°C.*

MAX6125 LOAD-TRANSIENT RESPONSE (SINKING)



10µs/div

A = OUTPUT CURRENT, 1mA/div, I_{OUT} = 0mA to -1mA
B = OUTPUT VOLTAGE, 200mV/div

MAX6125 LOAD-TRANSIENT RESPONSE (SOURCING)



10µs/div

A = OUTPUT CURRENT, 1mA/div, I_{OUT} = 0mA to 1mA
B = OUTPUT VOLTAGE, 50mV/div

MAX6125 LINE-TRANSIENT RESPONSE



5µs/div

A = INPUT VOLTAGE, 100mV/div, V_{IN} = 3V ±50mV
B = OUTPUT VOLTAGE, 20mV/div

MAX6125 0.1Hz TO 100Hz NOISE



1s/div

Pin Description

PIN			NAME	FUNCTION
SO	SOT23-3	SOT143		
1	2	4	OUT	Reference Output
2, 3, 5*, 6, 7	—	—	N.C.	No Connection. Not internally connected.
4	3	1	GND	Ground
5**	—	2	ADJ	Adjustable output voltage feedback input. Connect a resistor divider between OUT, ADJ, and GND (Figure 1).
8	1	3	IN	Input Voltage

*Except MAX6160.
**MAX6160 only.



Figure 1. MAX6160 Adjustable Output Circuit

Applications Information

Setting the MAX6160 Output Voltage

Set the output voltage on the MAX6160 by connecting a resistor divider between OUT, ADJ, and GND (Figure 1). Choose R1 according to the following equation:

$$R1 = (1.06 \times 10^5)(V_{OUT} / V_{ADJ})\ \Omega$$

where V_{TH} = 1.23V. The scaling factor (1.06×10^5) compensates for the MAX6160's change in ADJ input current over temperature. When R1 is chosen correctly, the change in voltage across R1 caused by the ADJ input current is properly cancelled. Choose R1 to within ±5% of this calculated value (nearest standard value plus specified resistor tolerance) to optimize the output voltage temperature coefficient. Using R1 = 215kΩ:

$$R2 = \frac{215k\Omega}{\left(\frac{2.5V}{1.23V} - 1\right)} \approx 208k\Omega$$

which is also the nearest 0.1% resistor value.

Choose R2 according to the following equation:

$$R2 = R1 / (V_{OUT} / V_{ADJ} - 1)$$

For example, a 2.5V output requires R1 = (1.06×10^5) (2.5V / 1.23V) ≈ 215kΩ, which is the nearest standard-value 0.1% resistor.

Input Bypassing

For the best line-transient performance, decouple the input with a 0.1µF ceramic capacitor, as shown in the *Typical Operating Circuit*. Locate the capacitor as close to the device pin as possible. Where transient performance is less important, no capacitor is necessary.

Output Bypassing

The MAX6125/MAX6141/MAX6145/MAX6150/MAX6160 do not require an output capacitor. They are stable for capacitive loads from 0nF to 10nF. If your application requires an output charge reservoir (e.g., to decouple the reference from a DAC's input), then make sure that the total output capacitive load does not exceed 10nF for optimum settling-time performance.

Ordering Information (continued)

PART	TEMP RANGE	PIN-PACKAGE	TOP MARK
MAX6145ESA	-40°C to +85°C	8 SO	—
MAX6145EUR-T	-40°C to +85°C	3 SOT23-3	EDAA
MAX6150ESA	-40°C to +85°C	8 SO	—
MAX6150EUR-T	-40°C to +85°C	3 SOT23-3	EEAA
MAX6160ESA	-40°C to +85°C	8 SO	—
MAX6160EUS-T	-40°C to +85°C	4 SOT143-4	JXAA

Chip Information

TRANSISTOR COUNT: 42

Typical Operating Circuit



Package Information

(The package drawing(s) in this data sheet may not reflect the most current specifications. For the latest package outline information go to **www.maxim-ic.com/packages**.)

SOT23 L.EPS

NOTES:
1. D&E DO NOT INCLUDE MOLD FLASH.
2. MOLD FLASH OR PROTRUSIONS NOT TO EXCEED .15mm (.006").
3. CONTROLLING DIMENSION: MILLIMETERS.
4. REFERENCE JEDEC TO236.
5. LEADS TO BE COPLANAR WITHIN 0.10mm.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
A	0.035	0.044	0.890	1.120
A1	0.001	0.004	0.013	0.100
B	0.015	0.020	0.370	0.510
C	0.003	0.071	0.085	0.180
D	0.110	0.120	2.800	3.040
E	0.047	0.055	1.200	1.400
e	0.070	0.081	1.780	2.050
H	0.083	0.104	2.100	2.640
L	0.008	0.017	0.210	0.420
L1	0.021 REF		0.54 REF	
S	0.018	0.024	0.45	0.60
α	0°	8°	0°	8°



TOP VIEW



FRONT VIEW



SIDE VIEW

DALLAS SEMICONDUCTOR MAXIM

PROPRIETARY INFORMATION

TITLE: PACKAGE OUTLINE, 3L SOT-23

APPROVAL	DOCUMENT CONTROL NO.	REV.	
	21-0051	E	1/1

Maxim cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim product. No circuit patent licenses are implied. Maxim reserves the right to change the circuitry and specifications without notice at any time.

© 2002 Maxim Integrated Products Printed USA MAXIM is a registered trademark of Maxim Integrated Products.