

USED ON MINI-APPL

D

1

□

THIS DRAWING IS A CONTROLLED DOCUMENT
DWG NO 687716-2
JUL 31, 1998
RELEASED FOR PUBLICATION
BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.
© COPYRIGHT 1998

APPLICATOR PARTS LIST						HARDWARE		BOLT, NUT, SCREW WASHER, ETC.			
NO.	DESCRIPTION	SIZE	LENGTH	REQ.	PART NO.	NO.	DESCRIPTION	SIZE	LENGTH	REQ.	PART NO.
101	4 SCREW, SHC	10-32	.50	2	3-21000-5	143	PIN, SLOTTED SPRING	Ø 1/8	.50	2	5-21028-1
102	SCREW, SHC	10-32	1.25	1	4-21000-0	144	5 PIN, SLOTTED SPRING	Ø 1/8	.25	1	9-21028-0
103	SCREW, SHC	10-32	1.50	1	4-21000-1	145	-	-	-	-	-
104	SCREW, SHC	10-32	.62	2	3-21000-6	146	-	-	-	-	-
105	SCREW, SHC	10-32	1.00	1	3-21000-9	147	SCREW, SOC HD SHLDR	Ø 1/4	1.00	1	21004-5
106	-	-	-	-	-	148	SCREW, SOC HD SHLDR	Ø 1/4	.25	1	5-21004-7
107	SCREW, SHC	10-32	1.00	2	3-21000-9	149	-	-	-	-	-
108	-	-	-	-	-	150	-	-	-	-	-
109	SCREW, SHC	8-32	.75	1	2-21000-9	151	WASHER, FLAT	#6	-	1	22260-5
110	SCREW, SHC	8-32	.75	2	2-21000-9	152	-	-	-	-	-
111	SCREW, SHC	8-32	.38	2	2-21000-6	153	-	-	-	-	-
112	SCREW, SHC	8-32	.62	2	2-21000-8	154	-	-	-	-	-
113	-	-	-	-	-	155	C-RING, RETAINING	Ø 3/16	-	2	21045-3
114	SCREW, RD HD MACH	6-32	1.50	1	3-21064-2	156	-	-	-	-	-
115	-	-	-	-	-	157	-	-	-	-	-
116	SCREW, BHC	1/4-20	.75	2	3-21002-5	158	SCREW, SOC SET	10-32	.25	1	5-21008-0
117	SCREW, BHC	1/4-20	.50	4	3-21002-3	159	SCREW, SOC SET	8-32	.38	1	4-21008-2
118	SCREW, BHC	10-32	.25	2	2-21002-5	160	-	-	-	-	-
119	SCREW, BHC	10-32	1.25	2	9-21002-0	161	-	-	-	-	-
120	-	-	-	-	-	162	-	-	-	-	-
121	-	-	-	-	-	163	-	-	-	-	-
122	SCREW, SOC SET	6-32	.25	1	3-23657-8	164	-	-	-	-	-
123	SCREW, SOC SET	1/4-20	.25	1	21009-2	165	-	-	-	-	-
124	SCREW, SHC	10-32	.38	1	3-21000-4	APPLICATOR ONLY TO INCLUDE					
125	-	-	-	-	-	-	-	-	-	-	-
126	NUT, HEX	10-32	-	1	21018-7	-	-	-	-	-	-
127	-	-	-	-	-	-	-	-	-	-	-
128	NUT, HEX	6-32	-	1	21068-5	-	-	-	-	-	-
129	-	-	-	-	-	-	-	-	-	-	-
130	WASHER, LOCK	#10	-	4	21024-5	-	-	-	-	-	-
131	WASHER, LOCK	#10	-	2	21024-5						
132	WASHER, LOCK	#8	-	2	21024-4						
133	WASHER, LOCK	#8	-	5	21024-4						
134	-	-	-	-	-						
135	-	-	-	-	-						
136	4 WASHER, LOCK	#10	-	2	21024-5						
137	-	-	-	-	-						
138	-	-	-	-	-						
139	PIN, DOWEL	Ø 3/16	1.50	1	1-21030-7						
140	PIN, DOWEL	Ø 3/16	.50	1	1-21030-1						
141	-	-	-	-	-						
142	6 PIN, SLOTTED SPRING	Ø 1/16	.25	REF	21028-2						

LOC
A
DIST
66

P	LTR	REVISION RECORD	DATE	DWN	APVD

FINISH -		DWN 7-12-92		MATERIAL M.O'BRINE		HEAT TREAT -							
DIMENSIONS: IN		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK 7-16-92		LEX KENSINGER							
		0 PLC ±		APVD 7-30-92		AMP AMP Incorporated Harrisburg, PA 17105-3608							
		1 PLC ±		NAME END FEED HDM APPLICATOR									
		2 PLC ±											
		3 PLC ±											
4 PLC ±		SCALE -		SIZE A3		DRAWING NO 687716-2		SHEET 2 OF 2		REV F1			
ANGLES± -		SURFACE TEXTURE ✓		CAGE CODE 00779		CUSTOMER AND ASSEMBLY DRAWING						RESTRICTED TO -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[687716-2](#)