


ELFF SERIES PART NUMBERING SCHEME

REV	ECN	APPD
-	3600	JC 12/11/98
A	4686	IQ 1/2/02
B	4792	IQ 3/11/02
C	4821	IQ 4/9/02
D	5742	2N 12/28/05



COLOR/PLATING
0=BLACK, TIN (STANDARD)
1=BLACK, SELECTIVE GOLD
G=GREEN, TIN
1G=GREEN, SEL. GOLD

MOUNTING EARS
0E=BLACK, TIN
1E=BLACK, SEL. GOLD
GE=GREEN, TIN
EG=GREEN, SEL. GOLD

CONSULT PCD FOR PART NO. AND
AVAILABILITY OF FOLLOWING OPTIONS:

- * CUSTOM COLORS
- * CUSTOM MARKING
- * CUSTOM KEYING
- * SELECTIVE CONTACT LOADING



RATINGS

CURRENT - 15A
VOLTAGE - 300V
U.L. FILE NO. E83421



RATINGS

CURRENT - 15A
VOLTAGE - 300V
CSA FILE NO. LR69703

DIN VDE 0627:1986
DIN VDE 0110-1:1989
EN 60947-1:1991
EN 60947-7-1:1992

CURRENT - 15A
VOLTAGE - 300V
TUV FILE NO. 20396

INSTALLATION RECOMMENDATIONS:

WIRE RANGE: AWG #14-26, STRANDED OR SOLID;
AWG #12 STRANDED
WIRE STRIP LENGTH: AWG #14-26: .310" (7.87mm)
AWG #12: .490" (12.45mm)
TIGHTENING TORQUE: 7 LB-IN.

MATERIALS:

HOUSING: PPO, UL 94 V-0
CONTACT: COPPER ALLOY, OPTIONAL FINISH
SCREW: STEEL, NICKEL FINISH
WIRE CLAMP: COPPER ALLOY, NICKEL FINISH

MAX OPERATING TEMPERATURE:
105°C

DIMENSIONS

ANSI Y14.5M
UNITS: INCHES
ACAD FILE

TOLERANCES

.XX ±.01
.XXX ±.005
ANGLES ±2°

PROJECTION



Amphenol Pcd SPECIFICATION DRAWING

ENGR

A. PATRIE 12/4/98

CHKD

APPD

J. CAHALY 12/11/98

TITLE

ELFF SERIES
PLUGGABLE TERMINAL BLOCK
FRONT / FRONT

ORIGINAL
STAMPED
IN RED

THIS DOCUMENT CONTAINS
PROPRIETARY INFORMATION WHICH
IS THE CONFIDENTIAL PROPERTY
OF AMPHENOL PCD INC. PEABODY, MA

SIZE

A

DWG NO.

ELFF02130


REV

D

CODE: 58982


SCALE: NONE

SHEET 1 OF 2




WITHOUT MOUNTING EARS



L=NUM OF POS X CL SPACING



TOP ACCESS




BOTTOM ACCESS




WITH MOUNTING EARS


L=NUM OF POS X CL SPACING



TOP ACCESS



BOTTOM ACCESS



SIZE

A

DWG NO.

ELFF02130

REV

D

CODE: 58982

SCALE: NONE

SHEET 2 OF 2