

Adapter Sub-D 9 Pin Buchse > Terminalblock 10 Pin

Kurzbeschreibung

Dieser Seriell zu Terminalblock Adapter ist für spezielle Industrieanwendungen geeignet, z.B. zum Anschluss einzelner Kabelstränge mit offenen Kabelenden.



Art.	65268
EAN	4043619652686
Ursprungsland	China
Zolltarifnummer	84718000

Abbildungen

Technische Daten

- Sub-D 9 Pin Buchse
- 10 Pin Terminalblock
- Pitch 3.81 mm

Packungsinhalt

- Adapter

Verpackung

- Delock Poly Bag

Adapter Sub-D 9 pin female > Terminal block 10 pin

Description

This Serial to Terminal block adapter is made for special industrial application e.g. for connecting single wires with open cable heads.



Ref.	65268
EAN	4043619652686
Country of origin	China
Customs tariff number	84718000

Images

Specification

- Sub-D 9 pin female
- 10 pin Terminal block
- Pitch 3.81 mm

Package content


- Adapter

Package

- Delock poly bag



WIRING TABLE	
DB9 PIN #	TERMINAL BLOCK #
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
SHELL	SHL

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	10/12/09	Liu Jian Ping




JACKSCREW DETAIL


2X #4-40 JACKSCREW




EVA, T=4mm



Part name:
Adapter terminal block > Sub-D 9 pin female




FEMALE. 9 CONTACT
D-SUB CONNECTOR



Electrical Character:

- 1> 100% open&short testing
- 2> With understanding voltage:DC 500 V 0.01 Sec.
- 3> Insulation Resistance: 50M Ohm (Min)
- 4> Conductive Resistance: 2 Ohm(Max)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN mm	APPROVALS	DATE	DELOCK® we move the world Item no. 65268 Barcode: 4043619652686 File: 88072
	DRAWN BY May	2/23/2011	
	CHECKED BY Gang	14/24/2011	
	APPROVED BY Steven	12/27/2010	
DIMENSIONAL TOLERANCES: .X = ±0.3 .XX = ±0.2 .XXX = ±0.1	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		
ANGULAR TOLERANCES: ALL = ± 1°			
PROJECTION 	COLOR VARIATIONS MAY OCCUR		