

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- , - .

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

MATERIAL:

HOUSING: NYLON, UL94V-0, BLACK.

TERMINAL: BRIGHT TIN PLATED, COPPER ALLOY.

SCREW: 6-32, STEEL, ZINC PLATED CLEAR

CHROMATE, UNLESS OTHERWISE STATED.

ELECTRICAL:

UL CLASS C: 20A, 150V.

UL CLASS D: 10A, 300V.

CSA TYPE B: 20A, 300V.

CSA TYPE C: 20A, 300V.

CSA TYPE D: 10A, 300V.


CSA TYPE E 20A, 300V.

WIRE RANGE: 12-22 AWG

MECHANICAL:

MAXIMUM TORQUE RATING: 7 IN-LB.

RECOMMENDED PCB LAYOUT



MIDDLE TERMINAL IS ROTATED 180° FROM OTHERS. NOT TO BE USED WITH RECOMMENDED PCB LAYOUT.



OBSOLETE PART NUMBER.



PRELIMINARY PART NUMBER.



SCREWS ARE NICKEL PLATED BRASS.






SEE FIGURE.



SPECIAL FULL THREAD BINDER HD SCREW USED FOR THIS ASSY ONLY ALLOWS FOR USE OF J4 JUMPER.



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



--

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN S SCHLEGEL 10/19/04

CHK S YODER 10/19/04

APVD S YODER 10/19/04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

—

CUSTOMER DRAWING

 TE Connectivity

NAME

4DB SERIES

P107 STYLE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1437667-6

SCALE NTS

SHEET

1 OF 2

REV D6

