



Hyperfast Rectifier, 8 A FRED Pt®



2L TO-220



FEATURES

- Hyperfast recovery time, extremely low Q_{rr}
- Isolated TO-220 2 pin
- High frequency PFC CCM operation
- 175 °C maximum operating junction temperature
- Low leakage current
- Compliant to RoHS directive 2002/95/EC
- Halogen-free according to IEC 61249-2-21 definition
- Designed and qualified for industrial level



RoHS
COMPLIANT
HALOGEN
FREE

DESCRIPTION

VS-8S2TH06I-M 600 V series are the state of the art tandem hyperfast recovery rectifiers: the new insulated 2 pin TO-220 package provide benchmark thermal resistance that coupled with excellent switching performance and low forward voltage drop allow this device to provide 8 A DC at 120 °C case temperature.

Specially designed for CCM PFC application, these devices show incomparable performance in every current intensive hard switching application.

Optimized reverse recovery stored charge enables downsizing of boosting switch and cooling system. Increased operating frequency make possible use of smaller reactive elements. Cost effective PFC application is then possible with high efficiency over wide input voltage range and loading factor.

The new ceramic insulated package warranty insulation up to 2 kV and features easy mounting together with not insulated parts, with minimum effect on R_{thJC} .

PRODUCT SUMMARY

Package	2L TO-220 Insulated
$I_{F(AV)}$	8 A
V_R	600 V
V_F at I_F	3.1 V
t_{rr} (typ.)	See Recovery table
T_J max.	175 °C
Diode variation	Doubler

ABSOLUTE MAXIMUM RATINGS FOR BOTH DIODES

PARAMETER	SYMBOL	TEST CONDITIONS	MAX.	UNITS
Repetitive peak reverse voltage	V_{RRM}		600	V
DC forward current	I_F	50 % duty cycle, rect. waveforms, $T_C = 120$ °C	8	A
Non-repetitive peak surge current	I_{FSM}	$T_C = 25$ °C	140	
Operating junction and storage temperatures	T_J, T_{Stg}		- 55 to 175	°C

ELECTRICAL SPECIFICATIONS FOR BOTH DIODES ($T_J = 25$ °C unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Breakdown voltage, blocking voltage	V_{BR}, V_R	$I_R = 100$ μ A	600	-	-	V
Forward voltage	V_F	$I_F = 8$ A	-	2.7	3.1	
		$I_F = 8$ A, $T_J = 125$ °C	-	2.1	2.3	
		$I_F = 8$ A, $T_J = 150$ °C	-	1.9	2.1	
Reverse leakage current	I_R	$V_R = V_R$ rated	-	< 1	10	μ A
		$T_J = 125$ °C, $V_R = V_R$ rated	-	7	50	
		$T_J = 150$ °C, $V_R = V_R$ rated	-	27	80	
Junction capacitance	C_T	$V_R = 600$ V	-	10.5	-	pF

DYNAMIC RECOVERY CHARACTERISTICS FOR BOTH DIODES (T _J = 25 °C unless otherwise specified)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNITS
Reverse recovery time	t _{rr}	I _F = 1.0 A, di _F /dt = - 50 A/μs, V _R = 30 V		-	13	20	ns
		T _J = 25 °C	I _F = 8 A di _F /dt = - 200 A/μs V _R = 390 V	-	11	16	
		T _J = 125 °C		-	23	30	
Peak recovery current	I _{RRM}	T _J = 25 °C		-	1.5	2.5	A
		T _J = 125 °C		-	2.8	3.7	
Reverse recovery charge	Q _{rr}	T _J = 25 °C		-	7	15	nC
		T _J = 125 °C		-	35	51	

THERMAL - MECHANICAL SPECIFICATIONS FOR BOTH DIODES						
PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNITS
Maximum junction and storage temperature range	T_J, T_{Stg}		- 55	-	175	°C
Thermal resistance, junction to case	R_{thJC}		-	2.30	2.85	°C/W
Thermal resistance, case to heatsink	R_{thCS}	Mounting surface, flat, smooth and greased	-	0.1	-	
Approximate weight			-	2.0	-	g
			-	0.07	-	oz.
Mounting torque			6.0 (5.0)	-	12 (10)	kgf · cm (lbf · in)
Marking device		Case style 2L TO-220	8S2TH06I			




Fig. 1 - Typical Forward Voltage Drop Characteristics




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage





Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage


Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics




Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current




Fig. 7 - Typical Reverse Recovery Time vs. dI_F/dt




Fig. 6 - Forward Power Loss Characteristics




Fig. 8 - Typical Stored Charge vs. dI_F/dt

Note

- (1) Formula used: $T_C = T_J - (P_d + P_{d_{REV}}) \times R_{thJC}$;
 P_d = Forward power loss = $I_{F(AV)} \times V_{FM}$ at $(I_{F(AV)}/D)$ (see fig. 6);
 $P_{d_{REV}}$ = Inverse power loss = $V_{R1} \times I_R (1 - D)$; I_R at $V_{R1} = 50\%$ rated V_R


**ORDERING INFORMATION TABLE**

Device code	VS-	8	S2	T	H	06	I	-M
	①	②	③	④	⑤	⑥	⑦	⑧
①	- Vishay Semiconductors product suffix							
②	- Current rating (8 = 8 A)							
③	- S2 = Doubler true 2 pin							
④	- T = TO-220							
⑤	- H = Hyperfast recovery							
⑥	- Voltage rating (06 = 600 V)							
⑦	- I = Insulated							
⑧	- Environmental digit:							
	-M = Halogen-free, RoHS compliant and terminations lead (Pb)-free							

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95171
Part marking information	www.vishay.com/doc?95170
SPICE model	www.vishay.com/doc?95257

TO-220-2L

DIMENSIONS in millimeters and inches



SYMBOL	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	4.420	4.720	0.174	0.186
A1	2.520	2.820	0.099	0.111
b	0.710	0.910	0.028	0.036
b1	1.170	1.370	0.046	0.054
c	0.360	0.460	0.014	0.018
c1	1.170	1.370	0.046	0.054
D	9.950	10.250	0.392	0.404
E	8.990	9.290	0.354	0.366
E1	12.550	12.850	0.494	0.506
e1	4.980	5.180	0.196	0.204
F	2.59	2.89	0.102	0.114
L	13.08	13.48	0.515	0.531
L1	3.47	3.87	0.136	0.152
Ø	3.79	3.89	0.149	0.153



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.