


10	9	8	7	6	5	4	3	2	19193
F									F
MATERIAL NO.	ENG. NO.	STUD SIZE	$\pm .003$ "S"	STOCK THICKNESS					
191930338	H-382-38	3/8	.390	.075 (1.90)					
191930336	H-382-12	1/2	.515						
191930339	H-382-58	5/8	.656						
191930337	H-382-34	3/4	.781						
191930340	H-382-78	7/8	.906						



SALES DRAWING

NOTE(S):
 1. MATERIAL: COPPER
 2. PLATING ELECTROPLATE TIN.
 3. ALL DIMENSIONS IN INCHES/(MM)
 4. WIRE SIZE: 1/0 AWG
 50 MM²

REVISED/UPDATE TO MX STD EC NO: ETC2003-035 DRW: DMYRICK 2003/08/20 CH'K'D: HEB 2003/08/21 APPR: RDEROSS 2003/08/21		QUALITY SYMBOLS ▼ = 0 △ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)	SCALE 2:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	REVISE ON CAD ONLY
		DESCRIPTION	mm INCH	DRAWN BY DLM 03/06/13		TITLE RING TONGUE TERMINAL VERSAKRIMP SERIES 1/0 AWG	
			4 PLACES $\pm ---$ $\pm ---$	DIMENSION STYLE IN/MM			
			3 PLACES $\pm ---$ $\pm .005$	DRAWN BY DLM 03/06/13			
			2 PLACES ± 0.13 $\pm .01$	CHECKED BY HEB 03/06/13			
			1 PLACE ± 0.25 $\pm ---$	APPROVED BY RWD 03/06/13		MOLEX INCORPORATED	
			ANGULAR $\pm 1/2^\circ$	(SEE CHART)		MATERIAL NO. SD-19193-021	DOCUMENT NO. 1 OF 1
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex](#):

[19193-0339](#)