


317-378 To 408

REF-09
(for E6020/1)




Set consisting of

Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 2 phenolic resin
mouldings
2 locknuts
>5kVdc
 $\geq 10^3$ megohms
1.41 Nm
1.6mm max

REF-11
(for L1850/1)




Set consisting of

Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 2 polypropylene resin
mouldings
2 locknuts
>5kVdc
 $\geq 10^3$ megohms
1.41 Nm
3.2mm max

REF-31A
(for L1001/1, L1499/1)




Set consisting of

Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 2 polyethylene
polypropylene
co-polymer mouldings
>8kVdc
 $\geq 10^6$ megohms
1.41 Nm
0.9 to 3.2mm max

REF-B
(for L1001/1, L1499/1, L1568/1)




Set consisting of

Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 1 phenolic resin moulding
1 SRBP insulating washer
>3kVdc
 $\geq 10^3$ megohms
1.41 Nm
0.9 to 1.6mm


REF-2B
(for L1001/1, L1499/1, L1568/1)



Set consisting of
Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

2 phenolic resin mouldings
>7kVdc
 $\geq 10^3$ megohms
1.41 Nm
0.9 to 1.6mm max


REF-CA
(for L1001/1, L1499/1, L1568/1)



Set consisting of
Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 1 polypropylene moulding
2 SRBP insulating washers
>3kV dc
 $\geq 10^3$ megohms
1.41 Nm
1.2mm to 3.2mm max


REF-F
(for L309/1)



Set consisting of
Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 1 phenolic resin moulding
1 SRBP insulating washer
1 metal washer
2 locknuts
>3kV dc
 $\geq 10^3$ megohms
2.1 Nm to 3.5 Nm
1.6 to 23.8mm max


REF-H
(for L1005/1)



Set consisting of
Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 1 phenolic resin moulding
1 micanite insulating washer
1 metal washer
2 locknuts
>4kV dc
 $\geq 10^3$ megohms
2.8 Nm to 3.5 Nm
1.6 to 23.8mm max

REF-2L
(for L1001/1, L1499/1)



Set consisting of
Breakdown voltage
Insulation resistance
Fixing torque
Panel thickness

{ 2 phenolic resin mouldings
>8kV dc
 $\geq 10^3$ megohms
1.41 Nm
0.9 to 4.8mm max

Fixing Kits

No 2
1 washer
1 soldertag
2 Locknuts (8-32 UNC)
(for L1499/1, L1568/1)

No 3
1 metal washer
1 non-rotating washer
2 Locknuts (2BA)
(for 1001/1)