



North America: Danboro, PA • E-mail: info@pemnet.com • Tel: +1-215-766-8853

Europe: Galway, Ireland • E-mail: europe@pemnet.com • Tel: +353-91-751714

Asia/Pacific: Singapore • E-mail: singapore@pemnet.com • Tel: +65-6-745-0660
Shanghai, China • E-mail: china@pemnet.com • Tel: +86-21-5868-3688

Part # STKB-M4-4, Molded-in Threaded Inserts, Thru-Threaded, Knurled - Metric

- Uniform knurl diameter reduces the risk of sink marks.
- Available in varying lengths for injection molding assemblies.
- Aluminum inserts ideal for light weight designs.
- Aluminum and stainless steel inserts offer lead-free alternative.



Specifications

Thread Size x Pitch	M4 x 0.7
Type	STKB
Thread Code¹	M4
Length Code	4
L - Length ± 0.13	4 mm
E Nom.	6.35 mm
Minor Dia.Min.	3.25 mm

Minor Dia.Max.	3.42 mm
Thread Specification	6H per ASME B1.13M
Standard Material	Free-machining, Leaded Brass
Standard Finish	Plain
CAD Supplier	PennEngineering® (SI®)

¹ Thread tapped thru, Class 3A/4h screw must pass with finger torque, but basic go gauge may stop at last thread.