


4

3

2

1

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			C1	REV PER ECR 09-026074	30NOV09	JR TM




- 1 TONGUE MATERIAL THK IS .027±.001
- 2 FOR .050 TO .105 WIRE INS. DIA.
- 3 MUST BE CRIMPED WITH 22-18 OR 22-16 PIDG (RED) TOOL.

- 4

 MEETS MS25036-147, CLASS 1 & 2
- 5

 MEETS MS25036-147, CLASS 2

2500	ON TAPE, REEL	5 54312-2	BODY: COPPER ASTM B152 TIN PL PER ASTM B545 SLEEVE: COPPER ASTM B152 TIN PL PER ASTM B545 INSULATION: NYLON, COLOR: YELLOW
1000	LOOSE PIECE	4 54312-1	
QTY	PACKAGE TYPE	PART NO	MATERIAL & FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH	27JAN04	Tyco Electronics Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK T MICHIELUTTI	27JAN04	NAME TERMINAL, NYLON PIDG, RING TONGUE; WIRE SIZE 26-24 —			
	0 PLC ± —	APVD T MICHIELUTTI	27JAN04				
	1 PLC ± —	PRODUCT SPEC —					
	2 PLC ± —	APPLICATION SPEC —					
MATERIAL SEE TABLE	FINISH SEE TABLE	3 PLC ± .008	WEIGHT —	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
		4 PLC ± —		A3	00779	C-54312	—
		ANGLES ± 1°					
CUSTOMER DRAWING				SCALE 8:1	SHEET 1 OF 1	REV C1	