



M68AW256M

4 Mbit (256K x16) 3.0V Asynchronous SRAM

FEATURES SUMMARY

- SUPPLY VOLTAGE: 2.7 to 3.6V
- 256K x 16 bits SRAM with OUTPUT ENABLE
- EQUAL CYCLE and ACCESS TIME: 55ns, 70ns
- SINGLE BYTE READ/WRITE
- LOW STANDBY CURRENT
- LOW V_{CC} DATA RETENTION: 1.5V
- TRI-STATE COMMON I/O
- AUTOMATIC POWER DOWN
- TSOP44, and TFBGA48 PACKAGES
 - Compliant with Lead-Free Soldering Processes
 - Standard or Lead-Free Option

Figure 1. Packages




TABLE OF CONTENTS

| | |
|--|-----------|
| FEATURES SUMMARY | 1 |
| Figure 1. Packages | 1 |
| SUMMARY DESCRIPTION | 4 |
| Figure 2. Logic Diagram | 4 |
| Table 1. Signal Names | 4 |
| Figure 3. TSOP Connections | 5 |
| Figure 4. TFBGA Connections (Top view through package) | 6 |
| Figure 5. Block Diagram | 7 |
| OPERATION | 8 |
| Output Disabled | 8 |
| Read Mode | 8 |
| Write Mode | 8 |
| Standby/Power-Down | 8 |
| Table 2. Operating Modes | 8 |
| MAXIMUM RATING | 9 |
| Table 3. Absolute Maximum Ratings | 9 |
| DC AND AC PARAMETERS | 10 |
| Table 4. Operating and AC Measurement Conditions | 10 |
| Figure 6. AC Measurement I/O Waveform | 10 |
| Figure 7. AC Measurement Load Circuit | 10 |
| Table 5. Capacitance | 11 |
| Table 6. DC Characteristics | 11 |
| Figure 8. Address Controlled, Read Mode AC Waveforms | 11 |
| Figure 9. Chip Enable or <u>Output</u> Enable Controlled, Read Mode AC Waveforms | 12 |
| Figure 10. Chip Enable or <u>UB/LB</u> Controlled, Standby Mode AC Waveforms | 12 |
| Table 7. Read and Standby Mode AC Characteristics | 13 |
| Figure 11. Write Enable Controlled, Write AC Waveforms | 14 |
| Figure 12. Chip Enable Controlled, Write AC Waveforms | 14 |
| Figure 13. <u>UB/LB</u> Controlled, Write AC Waveforms | 15 |
| Table 8. Write Mode AC Characteristics | 16 |
| Figure 14. Low V_{CC} Data Retention AC Waveforms | 17 |
| Table 9. Low V_{CC} Data Retention Characteristics | 17 |
| PACKAGE MECHANICAL | 18 |
| Figure 15. TSOP44 II - 44 lead Plastic Thin Small Outline Type II, Package Outline | 18 |
| Table 10. TSOP 44 II - 44 lead Plastic Thin Small Outline Type II, Package Mechanical Data | 18 |
| Figure 16. TFBGA48 6x8mm - 6x8 active ball array, 0.75 mm pitch, Bottom View Package Outline | 19 |
| Table 11. TFBGA48 6x8mm - 6x8 active ball array, 0.75 mm pitch, Package Mechanical Data | 19 |
| Figure 17. TFBGA48 7x8mm - 6x8 ball array, 0.75 mm pitch, Bottom View Package Outline | 20 |

| | |
|--|-----------|
| Table 12. TFBGA48 7x8mm - 6x8 ball array, 0.75 mm pitch, Package Mechanical Data | 20 |
| PART NUMBERING | 21 |
| Table 13. Ordering Information Scheme | 21 |
| REVISION HISTORY | 22 |
| Table 14. Document Revision History | 22 |

SUMMARY DESCRIPTION

The M68AW256M is a 4 Mbit (4,194,304 bit) CMOS SRAM, organized as 262,144 words by 16 bits. The device features fully static operation requiring no external clocks or timing strobes, with equal address access and cycle times. It requires a single 2.7 to 3.6V supply. This device has an automatic power-down feature, reducing the power consumption by over 99% when deselected.

The M68AW256 is available in TFBGA48 (6x8mm - 6x8 active ball array, 0.75mm pitch), TFBGA48

(7x8mm - 6x8 active ball array, 0.75 mm pitch) and in TSOP44 Type II packages.

In addition to the standard version, both packages are also available in Lead-free version, in compliance with the JEDEC Std J-STD-020B, the ST ECOPACK 7191395 Specification, and the RoHS (Restriction of Hazardous Substances) directive.

All packages are compliant with Lead-free soldering processes.

Figure 2. Logic Diagram




Table 1. Signal Names

| | |
|------------|-----------------------------------|
| A0-A17 | Address Inputs |
| DQ0-DQ15 | Data Input/Output |
| \bar{E} | Chip Enable |
| \bar{G} | Output Enable |
| \bar{W} | Write Enable |
| \bar{UB} | Upper Byte Enable Input |
| \bar{LB} | Lower Byte Enable Input |
| Vcc | Supply Voltage |
| Vss | Ground |
| NC | Not Connected Internally |
| DU | Don't Use as Internally Connected |

Figure 3. TSOP Connections




Figure 4. TFBGA Connections (Top view through package)





Figure 5. Block Diagram



OPERATION

The device has four standard operating modes: Output Disabled, Read, Write and Standby/Power-Down. These modes are determined by the control inputs \bar{E} , \bar{W} , \bar{G} , \bar{LB} and \bar{UB} as summarized in Table 2., Operating Modes.

Output Disabled. The Output Enable signal, \bar{G} , provides high-speed tri-state control of DQ0-DQ15, allowing fast read/write cycles on the I/O data bus. The device is in Output Disabled mode when Output Enable, \bar{G} , is High. In this mode, \bar{LB} and \bar{UB} are Don't care and DQ0-DQ15 are high impedance.

Read Mode. The M68AW256M is in the Read mode whenever Write Enable (\bar{W}) is High with Output Enable (\bar{G}) Low, and Chip Enable (\bar{E}) is asserted.

This provides access to data from eight or sixteen, depending on the status of the signal \bar{UB} and \bar{LB} , of the 4,194,304 locations in the static memory array, specified by the 18 address inputs. If only one of the Byte Enable inputs is at V_{IL} , the M68AW256M is in Byte Read mode. If the two Byte Enable inputs are at V_{IL} , the M68AW256M is in Word Read mode. So depending on the status of the \bar{UB} and \bar{LB} signals, valid data will be available on the lower eight, the upper eight or all sixteen output pins, t_{AVQV} after the last stable address, providing \bar{G} is Low and \bar{E} is Low.

If either of \bar{E} or \bar{G} is asserted after t_{AVQV} has elapsed, data access will be measured from the limiting parameter (t_{ELQV} , t_{GLQV} or t_{BLQV}) rather than the address. Data out may be indeterminate at t_{ELQX} , t_{GLQX} and t_{BLQX} but data lines will always be valid at t_{AVQV} .

Write Mode. The M68AW256M is in the Write mode whenever the \bar{W} and \bar{E} are Low. Either the Chip Enable input (\bar{E}) or the Write Enable input (\bar{W}) must be de-asserted during Address transitions for subsequent write cycles. When \bar{E} (\bar{W}) is Low, and \bar{UB} or \bar{LB} is Low, write cycle begins on the \bar{W} (\bar{E})'s falling edge. When \bar{E} and \bar{W} are Low, and $\bar{UB} = \bar{LB} = \text{High}$, write cycle begins on the first falling edge of \bar{UB} or \bar{LB} . Therefore, address setup time is referenced to Write Enable, Chip Enable or \bar{UB}/\bar{LB} as t_{AVWL} , t_{AVEL} and t_{AVBL} respectively, and is determined by the latter occurring edge.

The Write cycle can be terminated by the earlier rising edge of \bar{E} , \bar{W} or \bar{UB}/\bar{LB} . If the Output is enabled ($\bar{E} = \text{Low}$, $\bar{G} = \text{Low}$, \bar{LB} or $\bar{UB} = \text{Low}$), then \bar{W} will return the outputs to high impedance within t_{WLQZ} of its falling edge. Care must be taken to avoid bus contention in this type of operation. Data input must be valid for t_{DVWH} before the rising edge of Write Enable, or for t_{DVEH} before the rising edge of \bar{E} , or for t_{DVBH} before the rising edge of \bar{UB}/\bar{LB} whichever occurs first, and remain valid for t_{WHDX} , t_{EHDX} and t_{BHDX} respectively.

Standby/Power-Down. The M68AW256M has a Chip Enable power down feature which invokes an automatic standby mode whenever either Chip Enable is de-asserted ($\bar{E} = \text{High}$) or \bar{LB} and \bar{UB} are de-asserted (\bar{LB} and $\bar{UB} = \text{High}$). An Output Enable (\bar{G}) signal provides a high speed tri-state control, allowing fast read/write cycles to be achieved with the common I/O data bus. Operational modes are determined by device control inputs \bar{W} , \bar{E} , \bar{LB} and \bar{UB} as summarized in the Operating Modes table (see Table 2).

Table 2. Operating Modes

| Operation | \bar{E} | \bar{W} | \bar{G} | \bar{LB} | \bar{UB} | DQ0-DQ7 | DQ8-DQ15 | Power |
|------------------------------------|-----------|-----------|-----------|------------|------------|-------------|-------------|----------------------|
| Deselected (Standby/Power-Down) | V_{IH} | X | X | X | X | Hi-Z | Hi-Z | Standby (I_{SB}) |
| | X | X | X | V_{IH} | V_{IH} | Hi-Z | Hi-Z | Standby (I_{SB}) |
| Lower Byte Read | V_{IL} | V_{IH} | V_{IL} | V_{IL} | V_{IH} | Data Output | Hi-Z | Active (I_{CC}) |
| Lower Byte Write | V_{IL} | V_{IL} | X | V_{IL} | V_{IH} | Data Input | Hi-Z | Active (I_{CC}) |
| Output Disabled | V_{IL} | V_{IH} | V_{IH} | X | X | Hi-Z | Hi-Z | Active (I_{CC}) |
| Upper Byte Read | V_{IL} | V_{IH} | V_{IL} | V_{IH} | V_{IL} | Hi-Z | Data Output | Active (I_{CC}) |
| Upper Byte Write | V_{IL} | V_{IL} | X | V_{IH} | V_{IL} | Hi-Z | Data Input | Active (I_{CC}) |
| Word Read | V_{IL} | V_{IH} | V_{IL} | V_{IL} | V_{IL} | Data Output | Data Output | Active (I_{CC}) |
| Word Write | V_{IL} | V_{IL} | X | V_{IL} | V_{IL} | Data Input | Data Input | Active (I_{CC}) |
| Output Disabled | V_{IH} | X | V_{IH} | X | X | Hi-Z | Hi-Z | Active (I_{CC}) |

Note: 1. X = V_{IH} or V_{IL} .

MAXIMUM RATING

Stressing the device above the rating listed in the "Absolute Maximum Ratings" table may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in the Operating sections of this specification is not im-

plied. Exposure to Absolute Maximum Rating conditions for extended periods may affect device reliability. Refer also to the STMicroelectronics SURE Program and other relevant quality documents.

Table 3. Absolute Maximum Ratings

| Symbol | Parameter | Value | Unit |
|----------------|--|------------------------|------|
| $I_O^{(1)}$ | Output Current | 20 | mA |
| T_A | Ambient Operating Temperature | -55 to 125 | °C |
| T_{STG} | Storage Temperature | -65 to 150 | °C |
| T_{LEAD} | Lead Temperature during Soldering ⁽²⁾ | 260 ⁽³⁾ | °C |
| V_{CC} | Supply Voltage | -0.5 to 4.6 | V |
| $V_{IO}^{(4)}$ | Input or Output Voltage | -0.5 to $V_{CC} + 0.5$ | V |
| P_D | Power Dissipation | 1 | W |

Note: 1. One output at a time, not to exceed 1 second duration.

2. Compliant with the JEDEC Std J-STD-020B (for small body, Sn-Pb or Pb assembly), the ST ECOPACK® 7191395 specification, and the European directive on Restrictions on Hazardous Substances (RoHS) 2002/95/EU.

3. Not exceeding 250°C for more than 30s, and peaking at 260°C.

4. Up to a maximum operating V_{CC} of 3.6V only.

DC AND AC PARAMETERS

This section summarizes the operating and measurement conditions, as well as the DC and AC characteristics of the device. The parameters in the following DC and AC Characteristic tables are derived from tests performed under the Measure-

ment Conditions listed in the relevant tables. Designers should check that the operating conditions in their projects match the measurement conditions when using the quoted parameters.

Table 4. Operating and AC Measurement Conditions

| Parameter | | M68AW256M |
|--|---------|---|
| V _{CC} Supply Voltage | | 2.7 to 3.6V |
| Ambient Operating Temperature | Range 1 | 0 to 70°C |
| | Range 6 | -40 to 85°C |
| Load Capacitance (C _L) | | 30pF |
| Output Circuit Protection Resistance (R ₁) | | 3.0kΩ |
| Load Resistance (R ₂) | | 3.1kΩ |
| Input Rise and Fall Times | | 1ns/V |
| Input Pulse Voltages | | 0 to V _{CC} |
| Input and Output Timing Ref. Voltages | | V _{CC} /2 |
| Output Transition Timing Ref. Voltages | | V _{RL} = 0.3V _{CC} ; V _{RH} = 0.7V _{CC} |

Figure 6. AC Measurement I/O Waveform




Figure 7. AC Measurement Load Circuit




Table 5. Capacitance

| Symbol | Parameter ^(1,2) | Test Condition | Min | Max | Unit |
|------------------|---|-----------------------|-----|-----|------|
| C _{IN} | Input Capacitance on all pins (except DQ) | V _{IN} = 0V | | 8 | pF |
| C _{OUT} | Output Capacitance | V _{OUT} = 0V | | 10 | pF |


Note: 1. Sampled only, not 100% tested.
2. At T_A = 25°C, f = 1 MHz, V_{CC} = 3.0V.

Table 6. DC Characteristics

| Symbol | Parameter | Test Condition | -L | | -N | | Unit | |
|-----------------------------------|--------------------------------|---|------|-----------------------|------|-----------------------|------|----|
| | | | Min | Max | Min | Max | | |
| I _{CC1} ^(1,2) | Operating Supply Current | V _{CC} = 3.6V, f = 1/t _{AVAV} , I _{OUT} = 0mA | 70ns | | 20 | | 10 | mA |
| | | | 55ns | | 26 | | 15 | mA |
| I _{CC2} ⁽³⁾ | Operating Supply Current | V _{CC} = 3.6V, f = 1MHz, I _{OUT} = 0mA | | 2 | | 2 | mA | |
| I _{SB} | Standby Supply Current CMOS | V _{CC} = 3.6V, f = 0, E ≥ V _{CC} - 0.2V or LB=UB ≥ V _{CC} - 0.2V | | 20 | | 20 | μA | |
| I _{LI} | Input Leakage Current | 0V ≤ V _{IN} ≤ V _{CC} | -1 | 1 | -1 | 1 | μA | |
| I _{LO} | Output Leakage Current | 0V ≤ V _{OUT} ≤ V _{CC} ⁽⁴⁾ | -1 | 1 | -1 | 1 | μA | |
| V _{IH} | Input High Voltage | | 2.2 | V _{CC} + 0.3 | 2.2 | V _{CC} + 0.3 | V | |
| V _{IL} | Input Low Voltage | | -0.3 | 0.6 | -0.3 | 0.6 | V | |
| V _{OH} | Output High Voltage | I _{OH} = -1.0mA | 2.4 | | 2.4 | | V | |
| V _{OL} | Output Low Voltage | I _{OL} = 2.1mA | | 0.4 | | 0.4 | V | |


Note: 1. Average AC current, cycling at t_{AVAV} minimum.
2. E = V_{IL}, LB OR/AND UB = V_{IL}, V_{IN} = V_{IL} OR V_{IH}.
3. E ≤ 0.2V, LB OR/AND UB ≤ 0.2V, V_{IN} ≤ 0.2V OR V_{IN} ≥ V_{CC} - 0.2V.
4. Output disabled.

Figure 8. Address Controlled, Read Mode AC Waveforms



Note: E = Low, G = Low, W = High, UB = Low and/or LB = Low.

Figure 9. Chip Enable or Output Enable Controlled, Read Mode AC Waveforms.



Note: Write Enable (W) = High.

Figure 10. Chip Enable or \bar{UB}/\bar{LB} Controlled, Standby Mode AC Waveforms




Table 7. Read and Standby Mode AC Characteristics

| Symbol | Parameter | | M68AW256M | | Unit |
|--------------------|---|-----|-----------|----|------|
| | | | 55 | 70 | |
| t_{AVAV} | Read Cycle Time | Min | 55 | 70 | ns |
| t_{AVQV} | Address Valid to Output Valid | Max | 55 | 70 | ns |
| $t_{AXQX}^{(1)}$ | Data hold from address change | Min | 5 | 5 | ns |
| $t_{BHQZ}^{(2,3)}$ | Upper/Lower Byte Enable High to Output Hi-Z | Max | 20 | 25 | ns |
| t_{BLQV} | Upper/Lower Byte Enable Low to Output Valid | Max | 55 | 70 | ns |
| $t_{BLQX}^{(1)}$ | Upper/Lower Byte Enable Low to Output Transition | Min | 5 | 5 | ns |
| $t_{EHQZ}^{(2,3)}$ | Chip Enable High to Output Hi-Z | Max | 20 | 25 | ns |
| t_{ELQV} | Chip Enable Low to Output Valid | Max | 55 | 70 | ns |
| $t_{ELQX}^{(1)}$ | Chip Enable Low to Output Transition | Min | 5 | 5 | ns |
| $t_{GHQZ}^{(2,3)}$ | Output Enable High to Output Hi-Z | Max | 20 | 25 | ns |
| t_{GLQV} | Output Enable Low to Output Valid | Max | 25 | 35 | ns |
| $t_{GLQX}^{(2)}$ | Output Enable Low to Output Transition | Min | 5 | 5 | ns |
| $t_{PD}^{(4)}$ | Chip Enable or $\overline{UB}/\overline{LB}$ High to Power Down | Max | 0 | 0 | ns |
| $t_{PU}^{(4)}$ | Chip Enable or $\overline{UB}/\overline{LB}$ Low to Power Up | Min | 55 | 70 | ns |

Note: 1. Test conditions assume transition timing reference level = $0.3V_{CC}$ or $0.7V_{CC}$.

2. At any given temperature and voltage condition, t_{GHQZ} is less than t_{GLQX} , t_{BHQZ} is less than t_{BLQX} and t_{EHQZ} is less than t_{ELQX} for any given device.

3. These parameters are defined as the time at which the outputs achieve the open circuit conditions and are not referenced to output voltage levels.

4. Tested initially and after any design or process changes that may affect these parameters.

Figure 11. Write Enable Controlled, Write AC Waveforms




Figure 12. Chip Enable Controlled, Write AC Waveforms





Figure 13. $\overline{UB}/\overline{LB}$ Controlled, Write AC Waveforms


Note: 1. During this period DQ0-DQ15 are in output state and input signals should not be applied.

Table 8. Write Mode AC Characteristics

| Symbol | Parameter | | M68AW256M | | Unit | |
|------------------------------------|---|------------|-----------|----|------|----|
| | | | 55 | 70 | | |
| t _{AVAV} | Write Cycle Time | Min | 55 | 70 | ns | |
| t _{AVBH} | Address Valid to \overline{LB} , \overline{UB} High | Min | 45 | 60 | ns | |
| t _{AVBL} | Address Valid to \overline{LB} , \overline{UB} Low | Min | 0 | 0 | ns | |
| t _{AVEH} | Address Valid to Chip Enable High | Min | 45 | 60 | ns | |
| t _{AVEL} | Address valid to Chip Enable Low | Min | 0 | 0 | ns | |
| t _{AVWH} | Address Valid to Write Enable High | Min | 45 | 60 | ns | |
| t _{AVWL} | Address Valid to Write Enable Low | Min | 0 | 0 | ns | |
| t _{BHAX} | \overline{LB} , \overline{UB} High to Address Transition | Min | 0 | 0 | ns | |
| t _{BHDX} | \overline{LB} , \overline{UB} High to Input Transition | Min | 0 | 0 | ns | |
| t _{BLBH} | \overline{LB} , \overline{UB} Low to \overline{LB} , \overline{UB} High | Min | 45 | 60 | ns | |
| t _{BLEH} | \overline{LB} , \overline{UB} Low to Chip Enable High | Min | 45 | 60 | ns | |
| t _{BLWH} | \overline{LB} , \overline{UB} Low to Write Enable High | Min | 45 | 60 | ns | |
| t _{DVBH} | Input Valid to \overline{LB} , \overline{UB} High | Min | 25 | 30 | ns | |
| t _{DVEH} | Input Valid to Chip Enable High | Min | 25 | 30 | ns | |
| t _{DVWH} | Input Valid to Write Enable High | Min | 25 | 30 | ns | |
| t _{EHAX} | Chip Enable High to Address Transition | Min | 0 | 0 | ns | |
| t _{EHDX} | Chip enable High to Input Transition | Min | 0 | 0 | ns | |
| t _{ELBH} | Chip Enable Low to \overline{LB} , \overline{UB} High | Min | 45 | 60 | ns | |
| t _{ELEH} | Chip Enable Low to Chip Enable High | Min | 45 | 60 | ns | |
| t _{ELWH} | Chip Enable Low to Write Enable High | Min | 45 | 60 | ns | |
| t _{WHAX} | Write Enable High to Address Transition | Min | 0 | 0 | ns | |
| t _{WHDX} | Write Enable High to Input Transition | Min | 0 | 0 | ns | |
| t _{WHQX} ⁽¹⁾ | Write Enable High to Output Transition | Min | 5 | 5 | ns | |
| t _{WLBH} | Write Enable Low to \overline{LB} , \overline{UB} High | Min | 45 | 60 | ns | |
| t _{WLEH} | Write Enable Low to Chip Enable High | Min | 45 | 60 | ns | |
| t _{WLQZ} ^(1,2) | Write Enable Low to Output Hi-Z | Max | 20 | 20 | ns | |
| t _{WLWH} | Write Enable Low to Write Enable High | -L version | Min | 45 | 60 | ns |
| | | -N version | Min | 40 | 50 | ns |

Note: 1. At any given temperature and voltage condition, t_{WLQZ} is less than t_{WHQX} for any given device.

2. These parameters are defined as the time at which the outputs achieve the open circuit conditions and are not referenced to output voltage levels.

Figure 14. Low V_{CC} Data Retention AC WaveformsTable 9. Low V_{CC} Data Retention Characteristics

| Symbol | Parameter | Test Condition | Min | Typ | Max | Unit |
|-------------------|--|---|------------|-----|-----|---------|
| $I_{CCDR}^{(1)}$ | Supply Current (Data Retention) | $V_{CC} = 1.5V, \bar{E} \geq V_{CC} - 0.2V$ or $\bar{UB} = \bar{LB} \geq V_{CC} - 0.2V, f = 0^{(3)}$ | | 4.5 | 9 | μA |
| $t_{CDR}^{(1,2)}$ | Chip Deselected to Data Retention Time | | 0 | | | ns |
| $t_R^{(2)}$ | Operation Recovery Time | | t_{AVAV} | | | ns |
| $V_{DR}^{(1)}$ | Supply Voltage (Data Retention) | $\bar{E} \geq V_{CC} - 0.2V$ or $\bar{UB} = \bar{LB} \geq V_{CC} - 0.2V, f = 0$ | 1.5 | | | V |


Note: 1. All other Inputs at $V_{IH} \geq V_{CC} - 0.2V$ or $V_{IL} \leq 0.2V$.

2. Tested initially and after any design or process changes that may affect these parameters. t_{AVAV} is Read cycle time.

3. No input may exceed $V_{CC} + 0.2V$.

PACKAGE MECHANICAL

Figure 15. TSOP44 II - 44 lead Plastic Thin Small Outline Type II, Package Outline




Note: Drawing is not to scale.

Table 10. TSOP 44 II - 44 lead Plastic Thin Small Outline Type II, Package Mechanical Data

| Symbol | millimeters | | | inches | | |
|--------|-------------|-------|-------|--------|--------|--------|
| | Typ | Min | Max | Typ | Min | Max |
| A | | | 1.200 | | | 0.0472 |
| A1 | | 0.050 | 0.150 | | 0.0020 | 0.0059 |
| A2 | | 0.950 | 1.050 | | 0.0374 | 0.0413 |
| b | 0.350 | | | 0.0138 | | |
| c | | 0.120 | 0.210 | | 0.0047 | 0.0083 |
| D | 18.410 | - | - | 0.7248 | - | - |
| E | 11.760 | - | - | 0.4630 | - | - |
| E1 | 10.160 | - | - | 0.4000 | - | - |
| e | 0.800 | - | - | 0.0315 | - | - |
| L | 0.500 | 0.400 | 0.600 | 0.0197 | 0.0157 | 0.0236 |
| ZD | 0.805 | - | - | 0.0317 | - | - |
| alfa | | 0 | 5 | | 0 | 5 |
| CP | | | 0.100 | | | 0.0039 |
| N | 44 | | | 44 | | |

Figure 16. TFBGA48 6x8mm - 6x8 active ball array, 0.75 mm pitch, Bottom View Package Outline




Note: Drawing is not to scale.

Table 11. TFBGA48 6x8mm - 6x8 active ball array, 0.75 mm pitch, Package Mechanical Data

| Symbol | millimeters | | | inches | | |
|--------|-------------|-------|-------|--------|--------|--------|
| | Typ | Min | Max | Typ | Min | Max |
| A | | | 1.200 | | | 0.0472 |
| A1 | | 0.260 | | | 0.0102 | |
| A2 | | | 0.900 | | | 0.0354 |
| b | | 0.350 | 0.450 | | 0.0138 | 0.0177 |
| D | 6.000 | 5.900 | 6.100 | 0.2362 | 0.2323 | 0.2402 |
| D1 | 3.750 | – | – | 0.1476 | – | – |
| ddd | | | 0.100 | | | 0.0039 |
| E | 8.000 | 7.900 | 8.100 | 0.3150 | 0.3110 | 0.3189 |
| E1 | 5.250 | – | – | 0.2067 | – | – |
| e | 0.750 | – | – | 0.0295 | – | – |
| FD | 1.125 | – | – | 0.0443 | – | – |
| FE | 1.375 | – | – | 0.0541 | – | – |
| SD | 0.375 | – | – | 0.0148 | – | – |
| SE | 0.375 | – | – | 0.0148 | – | – |

M68AW256M

Figure 17. TFBGA48 7x8mm - 6x8 ball array, 0.75 mm pitch, Bottom View Package Outline



Note: Drawing is not to scale.

Table 12. TFBGA48 7x8mm - 6x8 ball array, 0.75 mm pitch, Package Mechanical Data

| Symbol | millimeters | | | inches | | |
|--------|-------------|-------|-------|--------|--------|--------|
| | Typ | Min | Max | Typ | Min | Max |
| A | | | 1.200 | | | 0.0472 |
| A1 | | 0.260 | | | 0.0102 | |
| A2 | | | 0.900 | | | 0.0354 |
| b | | 0.350 | 0.450 | | 0.0138 | 0.0177 |
| D | 7.000 | 6.900 | 7.100 | 0.2756 | 0.2717 | 0.2795 |
| D1 | 3.750 | – | – | 0.1476 | – | – |
| ddd | | | 0.100 | | | 0.0039 |
| E | 8.000 | 7.900 | 8.100 | 0.3150 | 0.3110 | 0.3189 |
| E1 | 5.250 | – | – | 0.2067 | – | – |
| e | 0.750 | – | – | 0.0295 | – | – |
| FD | 1.625 | – | – | 0.0640 | – | – |
| FE | 1.375 | – | – | 0.0541 | – | – |
| SD | 0.375 | – | – | 0.0148 | – | – |
| SE | 0.375 | – | – | 0.0148 | – | – |

PART NUMBERING

Table 13. Ordering Information Scheme

| Example: | M68AW256 | M | L | 55 | ZB | 6 | T |
|---|----------|---|---|----|----|---|---|
| Device Type M68 | | | | | | | |
| Mode A = Asynchronous | | | | | | | |
| Operating Voltage W = 2.7 to 3.6V | | | | | | | |
| Array Organization 256 = 4 Mbit (256K x16) | | | | | | | |
| Option 1 M = 1 Chip Enable; Write and Standby from \overline{UB} and \overline{LB} | | | | | | | |
| Option 2 L = L-Die N = N-Die | | | | | | | |
| Speed Class 55 = 55 ns 70 = 70 ns | | | | | | | |
| Package ND = TSOP 44 Type II ZH = TFBGA48 6x8mm - 6x8 ball array, 0.75 mm pitch ZB= TFBGA48 7x8mm - 6x8 ball array, 0.75 mm pitch | | | | | | | |
| Operative Temperature 1 = 0 to 70 °C 6 = -40 to 85 °C | | | | | | | |
| Shipping Blank = Standard Packing (Tray) T = Tape & Reel Packing E = Lead-Free Package, Standard Packing (Tray) F = Lead-Free Package, Tape and Reel Packing | | | | | | | |

For a list of available options (Speed, Package, etc...) or for further information on any aspect of this device, please contact the STMicroelectronics Sales Office nearest to you.

REVISION HISTORY

Table 14. Document Revision History

| Date | Version | Revision Details |
|---------------|---------|---|
| February 2002 | -01 | First Issue |
| 13-Mar-2002 | -02 | Tables 4, 7 and 9 clarified Figure 14 clarified |
| 17-Jun-2002 | -03 | I _{CCDR} clarified (Table 9) I _{SB} clarified (Table 6) |
| 09-Oct-2002 | 3.1 | Revision numbering modified: a minor revision will be indicated by incrementing the digit after the dot, and a major revision, by incrementing the digit before the dot (revision version 03 equals 3.0). Part number modified. |
| 20-Feb-2004 | 4.0 | TFBGA48 7x8 replaced by TFBGA48 6x7: Figure 16. , TFBGA48 6x8mm - 6x8 active ball array, 0.75 mm pitch, Bottom View Package Outline and Table 11. , TFBGA48 6x8mm - 6x8 active ball array, 0.75 mm pitch, Package Mechanical Data updated. I _{CC1} and I _{SB} updated in Table 6. , DC Characteristics . t _{WLWH} updated in Table 8. , Write Mode AC Characteristics . Minor content modifications. FEATURES SUMMARY , SUMMARY DESCRIPTION , Table 13. , Ordering Information Scheme updated with Package Lead-free information. TLEAD parameter added in Table 3. , Absolute Maximum Ratings . |
| 27-Apr-2004 | 5.0 | TFBGA48 7x8mm - 6x8 active ball array, 0.75mm pitch reintroduced. TFBGA 6x7mm -6x8mm active ball array replaced by TFBGA48 6x8mm- 6x8 active ball array, 0.75mm pitch. |

Information furnished is believed to be accurate and reliable. However, STMicroelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of STMicroelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. STMicroelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of STMicroelectronics.

The ST logo is a registered trademark of STMicroelectronics.
ECOPACK[®] is a registered trademark of STMicroelectronics.
All other names are the property of their respective owners.

© 2004 STMicroelectronics - All rights reserved

STMicroelectronics GROUP OF COMPANIES
Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany -
Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore -
Spain - Sweden - Switzerland - United Kingdom - United States
www.st.com