



PANDUIT PART NO. **	PANEL THICKNESS	A	B	C	D	E REF.	F * REF	G * REF
GE_36F-C	TO 0.036 (0.91)	0.025 (0.64)	0.045 (1.14)	0.087 (2.21)	0.030 (0.76)	0.106 (2.69)	.060	0.150 (3.81)
GE_62F-C	0.036 - 0.062 (0.91)-(1.57)	0.035 (0.89)	0.070 (1.78)	0.130 (3.30)	0.030 (0.76)	0.131 (3.33)	.105	0.150 (3.81)
GE_99F-C	0.062 - 0.099 (1.57)-(2.51)	0.054 (1.37)	0.108 (2.74)	0.155 (3.94)	0.030 (0.76)	0.169 (4.29)	.125	0.150 (3.81)
GE_144F-C	0.099 - 0.144 (2.51)-(3.66)	0.090 (2.29)	0.152 (3.86)	0.182 (4.66)	0.030 (0.76)	0.213 (5.41)	.160	0.150 (3.81)
GE_189F-C	0.144 - 0.189 (3.66)-(4.80)	0.12 (3.2)	0.206 (5.23)	0.255 (6.48)	0.046 (1.17)	0.297 (7.55)	—	—

GE S 36 F - C O
 WEATHER RESISTANT BLACK
 100 FOOT ROLL
 F=POLYETHYLENE
 MAX. PANEL THICKNESS
 IS=SOLID
 E=SLOTTED
 GROMMET EDGING



- 3) SEE CURRENT PRICE SHEET FOR PART NO. SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 4) COLOR: a) NATURAL
b) -0 AFTER PART NO. DENOTES WEATHER RESISTANT BLACK
- 5) SLOTTED WALL STYLE IS RECOMMENDED FOR INSIDE EDGE OF PANEL CUT OUTS.
SOLID WALL STYLE IS RECOMMENDED FOR STRAIGHT, OUTSIDE EDGES.

G00239FU_DC_03A.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

CONTINUOUS ROLL GROMMET EDGING

3	2/4/03	LGG		UPDATED DIM 'A' ON GE_189F-C WAS 0.125 (3.18)	GB0239FU	2						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.1(2.5) (.XXX) ±0.020(.5) (.XX) ±0.05(1.3) ANGLES ±5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	6/12/02	LGG		UPDATED DIM 'F' AS REFERENCE	GB0239FU	2									
1	4/10/02	LGG		CHG 'G' DIM TO REF	GB0239FU	1						DRAWN BY CEW	MAT'L: SEE NOTE #2	SCALE NONE	
R	6-5-98	CPE		ADDED NOTE #5, UPDATED FILE NAME	GB0239FU	R						DATE 5-24-85			DRAWING NO. GB0239FU
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP				CHK'D			