



VXI PT NO	MODEL NUMBER	FARNELL PT NO
14428-000	EPS 5/200C	118-6388
14429-000	EPS 12/100C	118-6389
14430-000	EPSP 12/50C	118-6390
14431-000	EPSP 15/40C	118-6391
14434-000	EPSP 5/200C	118-6392
14435-000	EPSP 12/100C	118-6394
14436-000	EPSPDL 12/50C	118-6396
14438-000	EPS 5/1000C	118-6397
14439-000	EPS 12/500C	118-6398
14440-000	EPS 15/400C	118-6399
14441-000	EPSP 12/250C	118-6400
14442-000	EPSP 15/200C	118-6402
14443-000	EPS 5T12C	118-6403
14444-000	EPS 5T15C	118-6404
14445-000	EPSP 5/1000C	118-6405
14446-000	EPSP 12/500C	118-6406
14534-000	EPSPDL 15/200C	118-6407



A comprehensive range of PCB mounting encapsulated power supplies available in either 120Vac or 230Vac input versions, and in single or dual output formats. They are vacuum encapsulated in flame retardant epoxy resin to UL94V0. All units incorporate overcurrent and reverse protection, and will automatically recover upon removal of the fault condition. The input and output pins are on 2.54mm, (0.1") centres for easy PCB mounting. All units also include a 'one shot' thermal fuse to protect against excessive over temperature conditions. The units are fully approved to EN60950 and are compliant to Low Voltage Directive.

PRODUCT SPECIFICATION & DIMENSIONS

47-63Hz
3KV AC RMS Input to Output
10mV Peak to peak (maximum)
All Outputs are short circuit protected
0°C to +40°C
0.155Kg





VxI POWER LIMITED

5 Watt Encapsulated AC-DC Linear Power Supply



PRODUCT DESCRIPTION

A comprehensive range of PCB mounting encapsulated power supplies with single, dual or triple output available in either 120Vac or 230Vac nominal input versions. The 5V crowbar, OVP and regulated DC output provides an ideal power supply solution for Microprocessors, OP Amps, TTL and CMOS applications. They are vacuum encapsulated in flame retardant epoxy resin to UL94V0. The range of units are capable of PCB Mounting or mechanical mounting using the base M3 bushes. The units are fully approved to EN60950 and are compliant to Low Voltage Directive.


Part Number	AC Input Range	Output Voltage 1	Output Voltage 2	Output Voltage 3	Output Current 1	Output Current 2	Output Current 3	Case
EPS 5/1000C	207-253V	5V	-	-	0-1000mA	-	-	A
EPS 12/500C	207-253V	12V	-	-	0-500mA	-	-	A
EPS 15/400C	207-253V	15V	-	-	0-400mA	-	-	A
EP5DL 12/250C	207-253V	+12V	-12V	-	0-250mA	0-250mA	-	A
EP5DL 15/200C	207-253V	+15V	-15V	-	0-200mA	0-200mA	-	A
EPS 5T12C	207-253V	+5V	+12V	-12V	0-300mA	0-150mA	0-150mA	B
EPS 5T15C	207-253V	+5V	+15V	-15V	0-300mA	0-120mA	0-120mA	B
EP5L 5/1000C	108-132V	5V	-	-	0-1000mA	-	-	A
EP5L 12/500C	108-132V	12V	-	-	0-500mA	-	-	A
EP5L 15/400C	108-132V	15V	-	-	0-400mA	-	-	A
EP5DL 12/250C	108-132V	+12V	-12V	-	0-250mA	0-250mA	-	A
EP5DL 15/200C	108-132V	+15V	-15V	-	0-200mA	0-200mA	-	A
EP5L 5T12C	108-132V	+5V	+12V	-12V	0-300mA	0-150mA	0-150mA	B
EP5L 5T15C	108-132V	+5V	+15V	-15V	0-300mA	0-120mA	0-120mA	B

PRODUCT SPECIFICATION & DIMENSIONS


Input Frequency Range 47-63Hz.
Isolation Test Voltage 3kV RMS.
Output Voltage Tolerance +/-5%.
Load Regulation (0-100%load) 100mV max all types.
Line Regulation 0.5% max
Operating Temperature Range 0°C to +40°C.

Output Protection All Outputs are short circuit protected.
Weight 0.50kg.
Output Ripple 4mV RMS max (5 volt units).
2mV RMS max (other units).

Note : The -V pin has no electrical connection on single o/p units.



CASE A



CASE B