

THIS DRAWING IS UNPUBLISHED.




RELEASED FOR PUBLICATION

, 19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

MOD	LOC	DIST	P	F	REVISIONS				
	GP	00			ZONE	LTR	DESCRIPTION	DATE	APPD
						M	REV PER OUE0-0037-01	17OCT01	JR



- 1 TO PREVENT THREAD STRIPPING, SCREW TORQUE SHOULD NOT EXCEED 9 IN LBS.
- 2 TAP HOLE IS 6-32UNC-2B, TWO MIN THREADS.
- 3 FINISH .000150 BRIGHT TIN-LEAD OVER .000050 NICKEL .

.57	YES	10	1-55323-0
.32	YES	6	55323-9
.57	NO	10	55323-6
.32	NO	6	55323-5
L	993879-1	NUMBER OF POSN	PART NO



SECTION A-A
SCALE 10:1
10 PLACES

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON:
2 PLC DEC ± -
3 PLC DEC ± .008
ANGLES ± -

MATERIAL
COPPER ALLOY 725,
.025 THICK

FINISH
3

DR 1-11-88
J.McCLINTON

CHK 1-11-88
R.STONE

APPD 1-15-88
M.GALLOWAY

APPD 1-15-88
M. GALLOWAY

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

AMP | AMP INCORPORATED
Harrisburg, Pa. 17105

NAME
TAP, POWER
DISTRIBUTION

SIZE
B

FSCM NO
00779

DRAWING NO
55323

SCALE
4:1

SHEET
1 OF 1