

## Description

Hall effect type current sensor with a single digital output factory programmed to go low when a given current threshold is exceeded. The TD Series is able to operate within a temperature range of -40° C to 125° C and has a fast response time of 1µs (typical). The miniature package size allows the TD series to be mounted on printed circuit boards and is integrated with an open collector digital output which is ideal for interfacing to control circuitry.

## Typical Applications

Welding equipment, servo drives, treadmills, automotive power conversion, power supplies, home audio, MRI equipment

## Ordering Information

### Type No

TD Over Current Detector

#### Trip Point

|     |         |
|-----|---------|
| 015 | 15 Amp  |
| 020 | 20 Amp  |
| 025 | 25 Amp  |
| 030 | 30 Amp  |
| 035 | 35 Amp  |
| 040 | 40 Amp  |
| 045 | 45 Amp  |
| 050 | 50 Amp  |
| 055 | 55 Amp  |
| 060 | 60 Amp  |
| 065 | 65 Amp  |
| 070 | 70 Amp  |
| 075 | 75 Amp  |
| 080 | 80 Amp  |
| 085 | 85 Amp  |
| 090 | 90 Amp  |
| 095 | 95 Amp  |
| 100 | 100 Amp |
| 105 | 105 Amp |
| 110 | 110 Amp |
| 115 | 115 Amp |
| 120 | 120 Amp |
| 125 | 125 Amp |

TD - 025 = ordering example



Series TD

## Technical Data

### Absolute Maximum Ratings

|                                                       |                                                                                           |
|-------------------------------------------------------|-------------------------------------------------------------------------------------------|
| Supply Voltage                                        | -1.0 to +25 VDC                                                                           |
| Voltage Externally Applied to Output                  | +25 VDC max (Output high, current below $I_{trip}$ )<br>-0.5 VDC min (Output high or low) |
| Output ON current (sink)                              | 50 mA                                                                                     |
| Operating Temp Range                                  | -40° C to +125° C                                                                         |
| Sensed Current                                        | +/- 500 Amp peak                                                                          |
| RMS voltage for AC isolation test, 50/60 Hz, 1 minute | 2.5 kVac                                                                                  |

Absolute maximum ratings are the extreme limits that the detector will withstand without damage. Electrical operation and characteristics are not guaranteed as the maximum limits are approached. Proper application of the detector must ensure that the detector operates within the operating characteristics below.

## Operating Characteristics

|                       | Symbol     | Min | Typ. | Max  | Notes                        |
|-----------------------|------------|-----|------|------|------------------------------|
| Supply Voltage        | $V_s$      | 3.8 |      | 24.0 | VDC                          |
| Supply Current        | $I_s$      |     |      | 10.0 | mA                           |
| Operating Temperature | $I_s$      | -40 |      | 125  | °C                           |
| Output Trip Time      | $T_{trip}$ |     | 1.0  | 2.5  | µS, $di/dt = I_{trip}/\mu S$ |
| Output ON Voltage     | $V_{os}$   |     | 0.15 | 0.40 | VDC sinking 20 mA            |
| Output ON Current     | $I_{os}$   |     |      | 20   | mA                           |

Note 1: Detector sensitive to unidirectional current as defined in mechanical dimension drawing

## Trip Currents (Amps @ 25° C)

| Trip Current | Min  | Max  |
|--------------|------|------|
| 15           | 13.2 | 16.8 |
| 20           | 17.6 | 22.4 |
| 25           | 22   | 28   |
| 30           | 26.4 | 33.6 |
| 35           | 30.8 | 39.2 |
| 40           | 35.2 | 44.8 |
| 45           | 39.6 | 50.4 |
| 50           | 44   | 56   |
| 55           | 48.4 | 61.6 |
| 60           | 52.8 | 67.2 |
| 65           | 57.2 | 72.8 |
| 70           | 61.6 | 78.4 |
| 75           | 66   | 84   |

| Trip Current | Min   | Max   |
|--------------|-------|-------|
| 80           | 70.4  | 89.6  |
| 85           | 74.8  | 95.2  |
| 90           | 79.2  | 100.8 |
| 95           | 83.6  | 106.4 |
| 100          | 88    | 112   |
| 105          | 92.4  | 117.6 |
| 110          | 96.8  | 123.2 |
| 115          | 101.2 | 128.8 |
| 120          | 105.6 | 134.4 |
| 125          | 110   | 140   |

## Trip Current vs. Temperature

Figure 1 - TD-025




Figure 2 - TD-030




Figure 3 - TD-035






Figure 4 - TD-040




## Trip Current vs. Temperature


**Figure 5 - TD-045**




**Figure 6 - TD-050**




**Figure 7 - TD-075**




**Figure 8 - TD-100**



**Figure 9 - TD-125**



## Mechanical Dimensions - A Package



Dimensions are in inches  
Dimensional tolerances unless otherwise  
specified: +/- 0.010"


| Pin | Desc. |
|-----|-------|
| 1   | Vo    |
| 2   | GND   |
| 3   | Vs    |
| 4   | Iin   |
| 5   | Iout  |

## Printed Circuit Board Mounting Footprint

Component side  
(component side view)



Solder side  
(component side view)



Hole Location Chart

| Hole | X      | Y       |
|------|--------|---------|
| A1   | 0.275" | -0.110" |
| A2   | 0.275" | -0.160" |
| A3   | 0.275" | -0.210" |
| C1   | 0.000  | 0.000   |
| C2   | 0.000  | -0.325" |

Hole Description Chart

| Hole | Finished diameter | Top Pad | Bottom Pad      |
|------|-------------------|---------|-----------------|
| A    | 0.027"            | 0.035"  | 0.035" x 0.100" |
| C    | 0.120"            | 0.200"  | 0.200"          |

### Notes:

1. Center aperture of detector located at C1, X=0.000, Y=0.000
2. Hole diameter tolerance +/- 0.003"
3. Hole location tolerance +/- 0.003"