BTA16-600CW3G, BTA16-800CW3G

Triacs

Silicon Bidirectional Thyristors

Designed for high performance full−wave ac control applications where high noise immunity and high commutating di/dt are required.

Features

- Blocking Voltage to 800 V
- On-State Current Rating of 16 A RMS at 25°C
- Uniform Gate Trigger Currents in Three Quadrants
- High Immunity to dV/dt − 1000 V/μs minimum at 125°C
- Minimizes Snubber Networks for Protection
- Industry Standard TO-220AB Package
- High Commutating dI/dt − 8.5 A/ms minimum at 125°C
- Internally Isolated (2500 V_{RMS})
- These are Pb−Free Devices

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Peak Repetitive Off−State Voltage (Note 1) (T_J = −40 to 125°C, Sine Wave, 50 to 60 Hz, Gate Open) BTA16−600CW3G BTA16−800CW3G	V_{DRM}, V_{RRM}	 600 800	V
On-State RMS Current (Full Cycle Sine Wave, 60 Hz, T_C = 25°C)	$I_{T(RMS)}$	16	A
Peak Non-Repetitive Surge Current (One Full Cycle Sine Wave, 60 Hz, T_C = 25°C)	I_{TSM}	170	A
Circuit Fusing Consideration (t = 8.3 ms)	I^2t	120	A^2sec
Non−Repetitive Surge Peak Off−State Voltage (T_J = 25°C, t = 10ms)	V_{DSM}/ V_{RSM}	V_{DSM}/V_{RSM} +100	V
Peak Gate Current (T_J = 125°C, t = 20 μs)	I_{GM}	4.0	A
Peak Gate Power (Pulse Width ≤ 1.0 μs, T_C = 80°C)	P_{GM}	20	W
Average Gate Power (T_J = 125°C)	$P_{G(AV)}$	1.0	W
Operating Junction Temperature Range	T_J	−40 to +125	°C
Storage Temperature Range	T_{stg}	−40 to +150	°C
RMS Isolation Voltage (t = 300 ms, R.H. ≤ 30%, T_A = 25°C)	V_{iso}	2500	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. V_{DRM} and V_{RRM} for all types can be applied on a continuous basis. Blocking voltages shall not be tested with a constant current source such that the voltage ratings of the devices are exceeded.

*For additional information on our Pb−Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor®

http://onsemi.com

TRIACS
16 AMPERES RMS
600 thru 800 VOLTS





TO−220AB
CASE 221A
STYLE 12

MARKING DIAGRAM



x	= 6 or 8
A	= Assembly Location
Y	= Year
WW	= Work Week
G	= Pb−Free Package

PIN ASSIGNMENT	
1	Main Terminal 1
2	Main Terminal 2
3	Gate
4	No Connection

ORDERING INFORMATION

Device	Package	Shipping
BTA16−600CW3G	TO−220AB (Pb−Free)	50 Units / Rail
BTA16−800CW3G	TO−220AB (Pb−Free)	50 Units / Rail

THERMAL CHARACTERISTICS

Characteristic	Symbol	Value	Unit
Thermal Resistance, Junction−to−Case (AC) Junction−to−Ambient	$R_{\theta JC}$ $R_{\theta JA}$	2.3 60	°C/W
Maximum Lead Temperature for Soldering Purposes 1/8″ from Case for 10 seconds	T_L	260	°C

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise noted; Electricals apply in both directions)

Characteristic		Symbol	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Peak Repetitive Blocking Current (V_D = Rated V_{DRM}, V_{RRM}; Gate Open)	T_J = 25°C T_J = 125°C	I_{DRM}, I_{RRM}	– –	– –	0.005 2.0	mA
ON CHARACTERISTICS						
Peak On-State Voltage (Note 2) (I_{TM} = ±22.5 A Peak)		V_{TM}	–	–	1.55	V
Gate Trigger Current (Continuous dc) (V_D = 12 V, R_L = 30 Ω) MT2(+), G(+) MT2(+), G(−) MT2(−), G(−)		I_{GT}	 2.0 2.0 2.0	 – – –	 35 35 35	mA
Holding Current (V_D = 12 V, Gate Open, Initiating Current = ±500 mA)		I_H	–	–	50	mA
Latching Current (V_D = 12 V, I_G = 1.2 x I_{GT}) MT2(+), G(+) MT2(+), G(−) MT2(−), G(−)		I_L	 – – –	 – – –	 60 65 60	mA
Gate Trigger Voltage (V_D = 12 V, R_L = 30 Ω) MT2(+), G(+) MT2(+), G(−) MT2(−), G(−)		V_{GT}	 0.5 0.5 0.5	 – – –	 1.7 1.1 1.1	V
Gate Non−Trigger Voltage (T_J = 125°C) MT2(+), G(+) MT2(+), G(−) MT2(−), G(−)		V_{GD}	 0.2 0.2 0.2	 – – –	 – – –	V
DYNAMIC CHARACTERISTICS						
Rate of Change of Commutating Current, See Figure 10. (Gate Open, T_J = 125°C, No Snubber)		$(dI/dt)_c$	8.5	–	–	A/ms
Critical Rate of Rise of On−State Current (T_J = 125°C, f = 120 Hz, I_G = 2 x I_{GT}, tr ≤ 100 ns)		dI/dt	–	–	50	A/μs
Critical Rate of Rise of Off-State Voltage (V_D = 0.66 x V_{DRM}, Exponential Waveform, Gate Open, T_J = 125°C)		dV/dt	1000	–	–	V/μs

2. Indicates Pulse Test: Pulse Width ≤ 2.0 ms, Duty Cycle ≤ 2%.

Voltage Current Characteristic of Triacs (Bidirectional Device)

Symbol	Parameter
V_{DRM}	Peak Repetitive Forward Off State Voltage
I_{DRM}	Peak Forward Blocking Current
V_{RRM}	Peak Repetitive Reverse Off State Voltage
I_{RRM}	Peak Reverse Blocking Current
V_{TM}	Maximum On State Voltage
I_H	Holding Current



Quadrant Definitions for a Triac



All polarities are referenced to MT1.
With in−phase signals (using standard AC lines) quadrants I and III are used.



Figure 1. RMS Current Derating



Figure 2. On-State Power Dissipation



Figure 3. On-State Characteristics



Figure 4. Thermal Response



Figure 5. Hold Current Variation



Figure 6. Gate Trigger Current Variation



Figure 7. Gate Trigger Voltage Variation



Note: Component values are for verification of rated $(di/dt)_c$. See AN1048 for additional information.

Figure 8. Simplified Test Circuit to Measure the Critical Rate of Rise of Commutating Current $(di/dt)_c$

PACKAGE DIMENSIONS

TO−220
CASE 221A−07
ISSUE O



NOTES:
1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION Z DEFINES A ZONE WHERE ALL BODY AND LEAD IRREGULARITIES ARE ALLOWED.

	INCHES		MILLIMETERS	
DIM	MIN	MAX	MIN	MAX
A	0.570	0.620	14.48	15.75
B	0.380	0.405	9.66	10.28
C	0.160	0.190	4.07	4.82
D	0.025	0.035	0.64	0.88
F	0.142	0.147	3.61	3.73
G	0.095	0.105	2.42	2.66
H	0.110	0.155	2.80	3.93
J	0.014	0.022	0.36	0.55
K	0.500	0.562	12.70	14.27
L	0.045	0.060	1.15	1.52
N	0.190	0.210	4.83	5.33
Q	0.100	0.120	2.54	3.04
R	0.080	0.110	2.04	2.79
S	0.045	0.055	1.15	1.39
T	0.235	0.255	5.97	6.47
U	0.000	0.050	0.00	1.27
V	0.045	---	1.15	---
Z	---	0.080	---	2.04

STYLE 12:
PIN 1. MAIN TERMINAL 1
2. MAIN TERMINAL 2
3. GATE
4. NOT CONNECTED

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303−675−2175 or 800−344−3860 Toll Free USA/Canada
Fax: 303−675−2176 or 800−344−3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800−282−9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81−3−5773−3850

ON Semiconductor Website: **www.onsemi.com**

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

BTA16−600CW3/D