

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

NOTES:






1. WIRE RANGE

CONDUCTOR: 0.3mm² - 0.75mm²

INSULATION DIA: 2.6mm MAX.

2. FOR CRIMPING DETAILS REFER

TO UTILUX CRIMP CHART NO. H25031




THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION. HARRISBURG, PENNSYLVANIA, USA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

ALL DIMENSIONS IN mm:

TOLERANCES UNLESS OTHERWISE SPECIFIED:	
DIMENSION (mm)	TOLERANCE (+/-mm)
LESS THAN 10	0.4
OVER 10 TO 30	0.5
OVER 30 TO 80	0.7
OVER 80 TO 250	1.0
ANGLES	±2°



MATERIAL

FINISH

DWN:

W.RIEDE 9.11.04

CHK:

H.THAU 9.11.04

APVD:

W.RIEDE 9.11.04

PRODUCT SPEC:

-

APPLICATION SPEC:

-

WEIGHT:

-

BRASS PRE-TIN

MATERIAL

RECEPTACLE H25031

DESCRIPTION

1-1627081-0

PART No.

tyco
Electronics

Tyco Electronics Corporation
AUSTRALIA

NAME:

RECEPTACLE QC 2.8 x 0.8

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

© 1627081

-

CUSTOMER DRAWING

SCALE 5:1

SHEET 1 OF 1

REV 0