

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026615110

Status:

Active

Overview:

Description:

3.96mm (.156") Pitch KK® Solid Header, Right Angle, with Friction Lock, 11 Circuits, Gold (Au) Plating

Documents:

- [3D Model](#)
- [Packaging Specification \(PDF\)](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-08-50 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family

Series

Application

Overview

Product Name

PCB Headers

41792

Wire-to-Board

KK®

KK®

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

Flammability

Glow-Wire Compliant

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Number of Rows

Orientation

PC Tail Length (in)

PC Tail Length (mm)

PCB Locator

PCB Retention

PCB Thickness Recommended (in)

PCB Thickness Recommended (mm)

Packaging Type

Pitch - Mating Interface (in)

Pitch - Mating Interface (mm)

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

11

11

Natural

50

94V-0

No

Yes

Brass

Gold

Polyester

1

Right Angle

0.156 In

3.96 mm

No

None

0.062 In

1.60 mm

Bag

0.156 In

3.96 mm

Yes

No

Partial

Yes

0°C to +75°C

Through Hole

Electrical

CSA

Current - Maximum

UL

Voltage - Maximum

LR19980

7A

E29179


250V

Material Info

Old Part Number

41792-0028

Reference - Drawing Numbers



Series image - Reference only

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Duration at Max.

Process Temperature
(seconds)

Lead-free Process
Capability

Max. Cycles at Max.

Process Temperature

Process Temperature
max. C

5

Wave Capable (TH
only)

1

235

Search Parts in this Series
41792 Series

Mates With
3069 , 2139 , 2145 , 6442 , 7674 , 7675 ,
41695 , L ink:41815

This document was generated on 11/05/2009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION