

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
AD	00		A2	REVISED PER ECO-12-011861	28JUN2012

- 1




HOUSING: LCP, UL94V-0, BLACK.
CONTACT: PHOSPHOR BRONZE.
POST: BRASS WIRE.
- 2

CONTACT: 0.76 μm GOLD PER ASTM B 488 IN CONTACT AREA,
1.27 μm MIN TIN-LEAD
ON PCB TAIL,
OVER 1.27μm MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST:1.27 μm MIN NICKEL.
- 3

PLATED THROUGH HOLE PER 114-13056,
FIGURE 4.
- 4

CONTACT: 0.76 μm GOLD PER ASTM B 488 IN CONTACT AREA,
1.27 μm MIN MATTE TIN PER ASTM B 545
ON PCB TAIL,
OVER 1.27 μm MIN NICKEL PER
SAE AMS-QQ-N-290 OVER ALL.
POST:1.27 μm MIN NICKEL.
- 6

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING
PER D.RENAUD/D.SINISI



6	OBSOLETE	4	SINGLE ENDED, NONSEQUENTIAL SIGNAL LEVEL 1, GROUND LEVEL 2	1410232-6
6	OBSOLETE	4	DIFFERENTIAL PAIR, NONSEQUENTIAL SIGNAL LEVEL 2, GROUND LEVEL 3	1410232-5
		4	SINGLE ENDED, NONSEQUENTIAL SIGNAL LEVEL 2, GROUND LEVEL 3	1410232-4
		2	SINGLE ENDED, NONSEQUENTIAL SIGNAL LEVEL 1, GROUND LEVEL 2	1410232-3
6	OBSOLETE	2	DIFFERENTIAL PAIR, NONSEQUENTIAL SIGNAL LEVEL 2, GROUND LEVEL 3	1410232-2
		2	SINGLE ENDED, NONSEQUENTIAL SIGNAL LEVEL 2, GROUND LEVEL 3	1410232-1
		FINISH	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.E. CONWELL	28SEP2001	 TE Connectivity	
DIMENSIONS:		CHK D. DEFIBAUGH	23OCT2001		
mm		APVD F.P. MORANA	23OCT2001	NAME	
		PRODUCT SPEC		RIGHT ANGLE, PLUG ASSEMBLY, LEFT END HALF, 25.4mm, MultiGig RT 1, DAUGHTERCARD CONNECTOR	
		108-2072			
		APPLICATION SPEC			
		114-13056			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		WEIGHT		SIZE	
0 PLC ±		-		CAGE CODE	
1 PLC ±				DRAWING NO	
2 PLC ±0.13				RESTRICTED TO	
3 PLC ±0.013				-	
4 PLC ±				A 100779	
ANGLES				C=1410232	
FINISH				SCALE	
1				8:1	
2				SHEET	
4				1 OF	
				REV	
				A2	