

T-3 DOUBLE CONTACT BAYONET BASE


HALOGEN LAMP

28V 25W

WAMCO PART NO.	ENVELOPE SIZE	BASE TYPE	RATING	FILAMENT SHAPE
WL-692	T-3	BA15d	28V 25W	CC-6

TEST VOLTS	CURRENT (A)			LIGHT OUTPUT (MSCP)			LIFE HRS
	MIN	NOM	MAX	MIN	NOM	MAX	
28V	.80	.89	.98	25.0	30.0	35.0	200

DIMENSIONAL CHARACTERISTICS



NOTES

1. Lamp clean with no foreign materials or glass chips inside
2. Envelope clear and free of scratches, discoloration, and any cement residue
3. Nickel-plated base
4. Part mark WL-692
5. RoHS compliant

