





DESCRIPTION: FEMALE - 0.283 RIGHT ANGLE / MACHINED - ECONOMY



No. OF PINS	DIMENSIONS							
	A	B	C	D	E	F	G	H
9	1.213	0.984	0.642	0.311	0.236	0.756	0.496	0.427
	30.80	24.99	16.30	7.90	5.99	19.20	12.60	10.85
15	1.541	1.312	0.970	0.311	0.236	1.091	0.496	0.427
	39.15	33.32	24.65	7.90	5.99	27.70	12.60	10.85
25	2.087	1.852	1.512	0.311	0.236	1.618	0.496	0.427
	53.00	47.04	38.40	7.90	5.99	41.10	12.60	10.85
37	2.728	2.500	2.157	0.311	0.236	2.256	0.496	0.427
	69.30	63.50	54.80	7.90	5.99	57.30	12.60	10.85
50	2.638	2.406	2.055	0.429	0.240	2.169	0.602	0.527
	67.00	61.11	52.20	10.90	6.10	55.10	15.30	13.39

173-EYY-21YRYY1

SERIES _____
POSITIONS _____
E09 _____
E15 _____
E25 _____
E37 _____
E50 _____
GENDER _____
2 = FEMALE _____
TERMINATION _____
1 = PC MOUNTING _____
SHELL PLATING _____
3 = NICKEL _____
RoHS COMPLIANT _____
HARDWARE OPTIONS _____
00 = NO HARDWARE _____
14 = SHORT BRACKET WITH 4-40 SCREW LOCK _____
24 = SHORT BRACKET WITH 4-40 SCREW _____
46 = BRACKET WITH 4-40 INSERT & BOARDLOCK _____
PLATING OPTIONS _____
1 = GOLD FLASH _____
2 = 30MICRO-INCH GOLD _____
3 = 50MICRO-INCH GOLD _____

MATERIAL:

SHELL: STEEL, NICKEL PLATED
INSULATOR: UL 94V-O RATED, WHITE PA6T
PROCESS TEMP.: 260° PROCESS TEMPERATURE
CONTACT: BRASS

ELECTRICAL:

CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 mOhms Max.
INSULATION RESISTANCE: 1,000 MOhms min.
VOLTAGE: 500VAC FOR 1 MINUTE
TEMPERATURE: -50° C TO 100° C

DO NOT SCALE FROM DRAWING

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN: WAYNE ROBBINS

CHECKED:

SCALE: 1 : 1

DWG NO. 173-EYY-21YRYY1

DATE: 11-28-05






DATE:

SHEET 1 OF 3

REV 9

NorComp

RoHS COMPLIANT




* TYP. ON ALL SIZES

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-08-06	
			CHECKED:		DATE:	
			SCALE: FULL		SHEET 2 OF 3	
NorComp		DWG NO. 173-EYY-21YRY1				
		REV 9				

173/174 SERIES



173 / 174 SERIES

14Y = SHORT BRACKET & 4-40
FEMALE HEX SOCKET
24Y = SHORT BRACKET & 4-40 SCREW



HARDWARE OPTIONS

REPLACE -YY IN LAST 3 DIGITS WITH OPTION CHOSEN


MATERIAL: COLD ROLLED STEEL

PLATING: CLEAR ZINC

46Y = BRACKET WITH 4-40 INSERT AND
BOARDLOCK



BRACKETS MOUNTED ON CONNECTOR



DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: PAM JENKINS		DATE: 11-28-05		
		CHECKED:		DATE:		
		SCALE: 1 : 1		SHEET 3 OF 3		REV 9
		DWG NO. 173-EYY-21YRYY1				