





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	E	REVISED PER ECO-18-008015	24MAY2018	AP	DG




Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



NOTES:

Insulator:PBT+G.F UL94V-O BLACK
Contact:PHOSPHOR BRONZE
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL
Holddown:Brass,100u" TIN OVER 50u" NICKEL
Sheet:Cold Roller Steel,Ni Plated
Rivetlock:Brass,Nickel Plated
LOT NUMBER "XXXX"
Stand For Calendar Year
Stand For Week Number

3.80 [0.150]	YES SEE DETAIL Z	30µ" Au	2311768-2
4.10 [0.161]	THREADED	30µ" Au	2311768-1
X ± 0.30 [± 0.012]	SCREWLOCK	Contact Area	P/N
BOARDLOCK LENGTH		Plating	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 11MAR2017	 TE Connectivity			
DIMENSIONS: mm		CHK DANIEL GORENC 11MAR2017				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD DANIEL GORENC 11MAR2017	NAME AMPLIMITE RECEPTACLE, HD22, RIGHT ANGLE, 26P - -			
		PRODUCT SPEC 108-130023				
		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C=2311768	RESTRICTED TO -
		MATERIAL -	FINISH -	WEIGHT		
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 of 1	REV E	