




LM3S800 Series Block Diagram. This block diagram shows the superset of features for the LM3S800 series of microcontrollers.

Features

32-Bit RISC Performance

- 32-bit ARM® Cortex™-M3 v7M architecture optimized for small-footprint embedded applications
- 50-MHz operation
- System timer (SysTick) provides a simple, 24-bit clear-on-write, decrementing, wrap-on-zero counter with a flexible control mechanism
- Thumb®-compatible Thumb-2-only instruction set processor core for high code density
- Integrated Nested Vectored Interrupt Controller (NVIC) provides deterministic interrupt handling
- 25 interrupt channels with eight priority levels
- Memory protection unit (MPU) provides a privileged mode for protected operating system functionality
- Unaligned data access enables data to be efficiently packed into memory
- Atomic bit manipulation (bit-banding) delivers maximum memory utilization and streamlined peripheral control

On-Chip Memory

- 64 KB single-cycle flash with two forms of flash protection on a 2-KB block basis
- 8 KB single-cycle SRAM

General-Purpose Timers

- Three General-Purpose Timer Modules (GPTM), each configurable as one 32-bit or two 16-bit timers with capture and simple PWM modes
- Real-Time Clock (RTC) capability

Watchdog Timer

- 32-bit down counter with a programmable load register
- Separate watchdog clock with an enable
- Programmable interrupt generation logic with interrupt masking
- Lock register protection from runaway software
- Reset generation logic with an enable/disable

Synchronous Serial Interface (SSI)

- Programmable interface operation for Freescale SPI, MICROWIRE, or Texas Instruments synchronous serial interfaces
- Master or slave operation

UART

- Two fully programmable 16C550-type UARTs
- Separate 16x8 transmit (TX) and 16x12 receive (RX) FIFOs to reduce CPU interrupt service loading
- Programmable baud-rate generator allowing speeds up to up to 3.125 Mbps

Analog Comparators

- Three independent integrated analog comparators
- Configurable for output to: drive an output pin or generate an interrupt
- Compare external pin input to external pin input or to internal programmable voltage reference

Inter-Integrated Circuit (I²C) Interface

- Master and slave receive and transmit operation with transmission speed up to 100 Kbps in Standard mode and 400 Kbps in Fast mode
- Interrupt generation
- Master with arbitration and clock synchronization, multimaster support, and 7-bit addressing mode

PWM

- Three PWM generator block, each with one 16-bit counter, two comparators, a PWM generator, and a dead-band generator
- Flexible output control block with PWM output enable of each PWM signal

Quadrature Encoder Inputs

- Hardware position integrator tracks the encoder position
- Velocity capture using built-in timer
- Interrupt generation on index pulse, velocity-timer expiration, direction change, and quadrature error detection

GPIOs

- 0-36 GPIOs, depending on configuration
- 5-V-tolerant input/outputs
- Programmable interrupt generation
- Programmable drive strength and slew-rate control

LM3S801 Microcontroller

STELLARIS®
microcontrollers

Power

- On-chip Low Drop-Out (LDO) voltage regulator, with programmable output user-adjustable from 2.25 V to 2.75 V
- Low-power options on controller: Sleep and Deep-sleep modes
- Low-power options for peripherals: software controls shutdown of individual peripherals
- User-enabled LDO unregulated voltage detection and automatic reset
- 3.3-V supply brown-out detection and reporting via interrupt or reset

Package and Temperature

- 48-pin RoHS-compliant LQFP and QFN packages
 - Industrial temperature (-40°C to +85°C)
 - Extended temperature (-40°C to +105°C)

Target Applications

- Factory automation and control
- Industrial control power devices
- Building and home automation
- Stepper motors
- Brushless DC motors
- AC induction motors



High-performance
ARM Cortex-M3
microcontroller for
real-time embedded
applications

Development Kit

The Stellaris® Family Development Kit provides the hardware and software tools that engineers need to

begin development quickly. Ask your distributor for part number DK-LM3S801. See the website for the latest tools available.



**Tools to begin
development quickly**

Ordering Information

Orderable Part Number	Description
LM3S801-IQN50-C2	Stellaris® LM3S801 Microcontroller Industrial Temperature 48-pin LQFP
LM3S801-IQN50-C2T	Stellaris® LM3S801 Microcontroller Industrial Temperature 48-pin LQFP Tape-and-reel
LM3S801-EQN50-C2	Stellaris® LM3S801 Microcontroller Extended Temperature 48-pin LQFP
LM3S801-EQN50-C2T	Stellaris® LM3S801 Microcontroller Extended Temperature 48-pin LQFP Tape-and-reel
LM3S801-IGZ50-C2	Stellaris® LM3S801 Microcontroller Industrial Temperature 48-pin QFN
LM3S801-IGZ50-C2T	Stellaris® LM3S801 Microcontroller Industrial Temperature 48-pin QFN Tape-and-reel
LM3S801-EGZ50-C2	Stellaris® LM3S801 Microcontroller Extended Temperature 48-pin QFN
LM3S801-EGZ50-C2T	Stellaris® LM3S801 Microcontroller Extended Temperature 48-pin QFN Tape-and-reel

Texas Instruments, Inc. • 108 Wild Basin, Suite 350 • Austin, TX 78746
Main: +1-512-279-8800 • Fax: +1-512-279-8879 • <http://www.luminarymicro.com>

Copyright © 2006-2009 Texas Instruments, Inc. All rights reserved. Stellaris and StellarisWare are registered trademarks of Texas Instruments. ARM and Thumb are registered trademarks and Cortex is a trademark of ARM Limited. Other names and brands may be claimed as the property of others.



IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

Products

Amplifiers	amplifier.ti.com
Data Converters	dataconverter.ti.com
DLP® Products	www.dlp.com
DSP	dsp.ti.com
Clocks and Timers	www.ti.com/clocks
Interface	interface.ti.com
Logic	logic.ti.com
Power Mgmt	power.ti.com
Microcontrollers	microcontroller.ti.com
RFID	www.ti-rfid.com
RF/IF and ZigBee® Solutions	www.ti.com/lprf

Applications

Audio	www.ti.com/audio
Automotive	www.ti.com/automotive
Broadband	www.ti.com/broadband
Digital Control	www.ti.com/digitalcontrol
Medical	www.ti.com/medical
Military	www.ti.com/military
Optical Networking	www.ti.com/opticalnetwork
Security	www.ti.com/security
Telephony	www.ti.com/telephony
Video & Imaging	www.ti.com/video
Wireless	www.ti.com/wireless

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265
Copyright © 2009, Texas Instruments Incorporated