


1, 2, 3, 4	1, 2, 3, 4	3.984	3.900	39	△	80	4-87422-
1	1	3.984	3.900	39	△	80	4-87422-
NONE	NONE	3.984	3.900	39	△	80	4-87422-
		3.884	3.800	38	↑	78	3-△
		3.784	3.700	37		76	3-△
		3.684	3.600	36		74	3-△
		3.584	3.500	35		72	3-△
		3.484	3.400	34		70	3-△
		3.384	3.300	33		68	3-△
		3.284	3.200	32		66	3-△
		3.184	3.100	31		64	3-△
		3.084	3.000	30		62	3-△
		2.984	2.900	29		60	3-△
		2.884	2.800	28		58	2-△
		2.784	2.700	27		56	2-△
		2.684	2.600	26		54	2-△
		2.584	2.500	25		52	2-△
		2.484	2.400	24		50	2-△
		2.384	2.300	23		48	2-△
		2.284	2.200	22		46	2-△
		2.184	2.100	21		44	2-△
		1.884	1.800	18		38	2-△
		1.784	1.700	17		36	2-△
		1.684	1.600	16		34	1-△
		1.584	1.500	15		32	1-△
		1.484	1.400	14		30	1-△
		1.384	1.300	13		28	1-△
		1.284	1.200	12		26	1-△
		1.184	1.100	11		24	1-△
		1.084	1.000	10		22	1-△
		.984	.900	9		20	1-△
		.884	.800	8		18	1-△
		.784	.700	7		16	1-△
		.684	.600	6		14	△
		.584	.500	5		12	△
		.484	.400	4		10	△
		.384	.300	3		8	△
		.284	.200	2		6	△
		.184	.100	1		4	△
		.084	—	—	↓	2	△
		2.084	2.000	20	△	42	△
		1.984	1.900	19	△	40	△
NONE	NONE	C	B	A	FINISH	NO. OF POSTS	PART NO
ROW N	ROW M						
POSTS OMITTED							

①. 000030 GOLD OVER 000050 NICKEL
2. TRUE POSITION TOLERANCE OF POST TIPS APPLIES WHEN
HEADERS ARE HELD FLAT AGAINST PRINTED CIRCUIT BOARD.
③ OBSOLETE PART NUMBER
④ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



UNLESS OTHERWISE
SPECIFIED DIMENSIONS
ARE IN INCHES.

TOLERANCES ON:

DECIMALS	$\pm .005$
ANGLES	$\pm$

MATERIAL
POSTS: PHOS BRONZE
HOUSING: GLASS FILLED
NYLON

FINISH	SEE TABLE
--------	-----------

CONTRACT NO

DR BAH 2-20-75

CHK *DM* *Witt* 2-20-75

APPD *B. Bennett 2/24/75*

APPD
R. Clark 2/24/75

DSGN APPD

OTHER APPD



AMP INCORPORATED
Harrisburg, Pa.

NAME _____

HEADER ASSEMBLY, MOD II,
.100x.100 &.025 SQ. POSTS

SIZE	CODE	IDENT NO	DRAWING NO
------	------	----------	------------

C 00779

87422

SCALE

SHEET