




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MATERIAL	MAX. BUNDLE DIA [mm]	LENGTH L ± .1 [mm]
MS4W63T15-L4	304	4" [102]	18.0" [457]
MS4W63T15-L6	316		
MS6W63T15-L4	304	6" [152]	24.4" [620]
MS6W63T15-L6	316		
MS8W63T15-L4	304	8" [203]	30.7" [780]
MS8W63T15-L6	316		
MS10W63T15-L4	304	10" [254]	37.0" [940]
MS10W63T15-L6	316		



- NOTES: 1. APPLICATION TOOLS: BT2MS75, BT1HT
2. ALL DIMENSIONS IN [] ARE mm.
3. FOR MATERIAL SEE TABLE.
4. TOLERANCES (UNLESS OTHERWISE SPECIFIED):
.X ± .03 [.8]
.XX ± .02 [.5]
.XXX ± .01 [.25]



S41152_02

02	11/06	MIM	SKB	#1 BODY EDGE WAS A #5 BODY EDGE	S500263	CCH	JJB	PANDUIT CORP. TINLEY PARK, ILLINOIS METAL STRAPPING .625 [15.88mm] WIDE			
01	9/03	BRH		CHG'D TO MS10W63T15-L4, WAS MS8W63T15-L4	11892						
00	9/03	BRH	EJD	RELEASED	11155	CCH	JJB				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST	DRAWN BY BRH	CHK'D EJD	SCALE FULL	DRAWING NO. S41152