






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AJ	16	A		REVISED PER EC OS14-0150-05	30AUG05	BM JL



- 1 ZINC PER QQ-Z-363.
- 2 POLYMETHYLPENTENE PER ASTM-D-1238.
- 3 PHOSPHOR BRONZE PER QQ-B-750.
- 4 BRASS PER ASTM-B-453.
- 5 BRASS PER ASTM-B-16.
- 6 NICKEL PLATE PER QQ-N-290, 3.81μm [.000150] MINIMUM THICK.
- 7 TIN PLATE PER ASTM-B-545, 3.81μm [.000150] MINIMUM THICK.
- 8 GOLD PLATE PER ASTM-B-488, 0.76μm [.000030] MINIMUM THICK.
- 9. SEE INSTRUCTION SHEET 408-2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

5227673-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN VARELA - 20APR2005 CHK J. HAVENER - 20APR2005 APVD J. LIPPERT - 20APR2005				Tyco Electronics Corporation Harrisburg, Pa 17105-3608			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		JACK, VERTICAL, PCB, 50 OHM, SERIES BNC					
		0 PLC ± -		PRODUCT SPEC 108-12078		-					
		1 PLC ± -									
		2 PLC ± 0.05 [.002]		APPLICATION SPEC		-					
		3 PLC ± -									
4 PLC ± -		5 PLC ± -		SIZE		CAGE CODE		DRAWING NO			
MATERIAL SEE NOTES 1-5		FINISH SEE NOTES 6-8		WEIGHT -		A1		00779		C=5227673	
CUSTOMER DRAWING				SCALE		4:1		SHEET		1 OF 1	
								REV		A	