

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0917911506

Status:


Active

Overview:

RAST Power Connector

Description:

5.00mm Pitch Appli-Mate RAST Power IDT Housing, 10 Amp, Indirect, Female, 3 Circuits, No Coding Keys Removed, Latch Between 2 & 3, Polarizing Rib Between Circuits 1 & 2, Glow-Wire Capable



Documents:

Drawing (PDF)

Product Specification 916270001-000 (PDF)

Application Specification 916270001-002 (PDF)

Application Specification AS-91627-001 (PDF)

Packaging Specification 916270001-001 (PDF)

Packaging Specification PK-91627-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	IDT and Solder Connectors
Series	91791
Comments	<p>""This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""</p> <p>""This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.""</p> <p>Yes</p>
Crimp Quality Equipment	

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

91791 Series

Overview	RAST Power Connector
Product Name	RAST Power
UPC	884982756854
Use With	RAST standard Interface
Physical	
Circuits (Loaded)	3
Circuits (maximum)	3
Color - Resin	Natural (White)
Durability (mating cycles max)	10
Flammability	94V-2
Gender	Female
Glow-Wire Capable	Yes
Lock to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Material - Resin	Nylon
Net Weight	1.686/g
Number of Rows	1
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C
Termination Interface: Style	IDT or Pierce
Wire Size AWG	18, 20, 22, 24
Electrical	
Current - Maximum per Contact	10.0A
Voltage - Maximum	250V AC
Material Info	
Reference - Drawing Numbers	
Application Specification	916270001-002, AS-91627-001
Packaging Specification	916270001-001, PK-91627-001-001
Product Specification	916270001-000
Sales Drawing	917910001-000, SD-93322-001

This document was generated on 01/31/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION